


FWP72 series

72 Watt AC Adapter with PFC



Features

Wide range AC input
Fully regulated output
High efficiency
Power Factor Correction (PFC) circuit
5 year warranty

Environmental

Operating temperature..... 0° C to 40° C
Storage temperature..... -55° C to 85° C
Weight = 2.05 lbs


EMI

Meets FCC class B, CISPR 22 class B

Safety

CSA Certified to CSA 950
NRTL/C : UL 1950, CSA 950
CE-Marked

Polarity	1	2	3	4	5
DIN-5	Com	Com	+V	Com	+V



Electrical Specifications

Input

Voltage..... 100 - 240 VAC
Current..... 2.0 Amp @ 100 VAC
Frequency..... 47 - 63 Hz
AC cord..... Optional
Input connector..... 3 Pin IEC 320 input receptacle

Output

Line regulation..... TYP +/- 1%
Load regulation..... TYP +/- 5%
Set point..... +/- 3% at 60% load
Hold up time..... 20 ms min at full load, 115 VAC
Over voltage protection..... Built-in
Over current protection..... Built-in
Short circuit protection..... Pulsing mode, auto recovery
Efficiency..... 80% min at full load and 115 VAC
Transient response..... 2 ms for 50% load change typical
Ripple/noise (V_{p-p})..... +/- 1% (20 MHz bandwidth)
Output connector..... 5 pin DIN

Model No.	Voltage	Power	Current
FWP7212-D5-NC	12V	72W	6.0A
FWP7215-D5-NC	15V	72W	4.8A
FWP7218-D5-NC	18V	72W	4.0A
FWP7224-D5-NC	24V	72W	3.0A
FWP7248-D5-NC	48V	72W	1.5A
FWP72-48-D5-NC	-48V	72W	1.5A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Elpac \(ICCNexergy\):](#)

[FWP7224-D5](#) [FWP72-48-D5](#) [FWP7212-D5](#) [FWP7215-D5](#) [FWP7218-D5](#) [FWP7248-D5](#) [FWP7248-D5F](#) [FWP7218-D5F](#) [FWP7224-D5F](#) [FWP7212-D5F](#) [FWP7215-D5F](#)