


Split Loom Tubing

561-SL250PE, 561-SL375PE, 561-SL500PE, 561-SL625PE, 561-SL750PE, 561-SL1000PE, 561-SL250PP, 561-SL375PP, 561-SL500PP, 561-SL625PP, 561-SL750PP, 561-SL1000PP, 561-SL250FRPP, 561-SL375FRPP, 561-SL500FRPP, 561-SL625FRPP, 561-SL750FRPP, 561-SL1000FRPP, 561-SL250NYGY, 561-SL375NYGY, 561-SL500NYGY, 561-SL625NYGY, 561-SL750NYGY, 561-SL1000NYGY

DIMENSIONS: in.

Date Last Revised: 11-13-12



MOUSER STOCK NO.	Description	A	B	C	Package Type
561-SL250PE	1/4" Polyethylene	0.266 (ref.)	0.395 (ref.)	0.120 (ref.)	100" Coil
561-SL375PE	3/8" Polyethylene	0.419 (ref.)	0.535 (ref.)	0.128 (ref.)	100" Coil
561-SL500PE	1/2" Polyethylene	0.505 (ref.)	0.670 (ref.)	0.143 (ref.)	100" Coil
561-SL625PE	5/8" Polyethylene	0.650 (ref.)	0.825 (ref.)	0.145 (ref.)	100" Coil
561-SL750PE	3/4" Polyethylene	0.761 (ref.)	0.927 (ref.)	0.144 (ref.)	100" Coil
561-SL1000PE	1" Polyethylene	0.909 (ref.)	1.033 (ref.)	0.172 (ref.)	100" Coil
561-SL250PP	1/4" Polypropylene	0.266 (ref.)	0.395 (ref.)	0.120 (ref.)	100" Coil
561-SL375PP	3/8" Polypropylene	0.419 (ref.)	0.535 (ref.)	0.128 (ref.)	100" Coil
561-SL500PP	1/2" Polypropylene	0.505 (ref.)	0.670 (ref.)	0.143 (ref.)	100" Coil
561-SL625PP	5/8" Polypropylene	0.650 (ref.)	0.825 (ref.)	0.145 (ref.)	100" Coil
561-SL750PP	3/4" Polypropylene	0.761 (ref.)	0.927 (ref.)	0.144 (ref.)	100" Coil
561-SL1000PP	1" Polypropylene	0.909 (ref.)	1.033 (ref.)	0.172 (ref.)	100" Coil
561-SL250FRPP	1/4" Flame Retardent Polypropylene	0.266 (ref.)	0.395 (ref.)	0.120 (ref.)	100" Coil
561-SL375FRPP	3/8" Flame Retardent Polypropylene	0.419 (ref.)	0.535 (ref.)	0.128 (ref.)	100" Coil
561-SL500FRPP	1/2" Flame Retardent Polypropylene	0.505 (ref.)	0.670 (ref.)	0.143 (ref.)	100" Coil
561-SL625FRPP	5/8" Flame Retardent Polypropylene	0.650 (ref.)	0.825 (ref.)	0.145 (ref.)	100" Coil
561-SL750FRPP	3/4" Flame Retardent Polypropylene	0.761 (ref.)	0.927 (ref.)	0.144 (ref.)	100" Coil
561-SL1000FRPP	1" Flame Retardent Polypropylene	0.909 (ref.)	1.033 (ref.)	0.172 (ref.)	100" Coil
561-SL250NYGY	1/4" Nylon	0.266 (ref.)	0.395 (ref.)	0.120 (ref.)	100" Coil
561-SL375NYGY	3/8" Nylon	0.419 (ref.)	0.535 (ref.)	0.128 (ref.)	100" Coil
561-SL500NYGY	1/2" Nylon	0.505 (ref.)	0.670 (ref.)	0.143 (ref.)	100" Coil
561-SL625NYGY	5/8" Nylon	0.650 (ref.)	0.825 (ref.)	0.145 (ref.)	100" Coil
561-SL750NYGY	3/4" Nylon	0.761 (ref.)	0.927 (ref.)	0.144 (ref.)	100" Coil
561-SL1000NYGY	1" Nylon	0.909 (ref.)	1.033 (ref.)	0.172 (ref.)	100" Coil

SPECIFICATIONS

All split loom is manufactured in Black

All nylon split loom has a Gray stripe for identification

All FR polypropylene split loom has a blue stripe

RoHS Compliant

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200898

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-SL250PE](#) [561-SL500PE](#) [561-SL375PE](#) [561-SL625FRPP](#) [561-SL750PP](#) [561-SL1000FRPP](#) [561-SL1000PP](#)
[561-SL375PP](#) [561-SL750FRPP](#) [561-SL250NYGY](#) [561-SL500NYGY](#) [561-SL250PP](#) [561-SL750NYGY](#) [561-SL1000PE](#)
[561-SL250FRPP](#) [561-SL625NYGY](#) [561-SL750PE](#) [561-SL375NYGY](#) [561-SL1000NYGY](#) [561-SL500PP](#) [561-](#)
[SL500FRPP](#) [561-SL375FRPP](#) [561-SL625PP](#) [561-SL625PE](#)