



Region
Global > North America > Europe

English | 中文 (简体) | 日本語

Part Number Search

Search

Home Products Search Support About Us

Home > Search Engine > Catalog: CSTCE14M7V53-R0

Resonators > CERALOCK (MHz) > Part Number

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specifications

Global Part Number	CSTCE14M7V53-R0
Previous Part Number	
Nominal Frequency	14.746MHz
Initial Tolerance	±0.5%
Resonant Frequency	40ohm
Temp. Stability	±0.3%
Operating Temperature Range	-20 to +80°C
Frequency Aging	±0.3%
Wash	Not Available
Ultrasonic Wash	Not Available
Built-in Load Capacitance	15pF
Use	For consumer electronics

Details

- [Part Numbering](#)
- [Appearance](#)
- [Dimensions](#)
- [Features_and_Applications](#)
- [Temperature_Characteristics](#)
- [Basic_Oscillation_Circuit](#)
- [Standard_Land_Pattern](#)
- [Notice_\(Storage_and_Operating_Conditions\)](#)
- [Notice_\(Rating\)](#)
- [Notice_\(Soldering_and_Mounting\)](#)
- [Notice_\(Handling\)](#)
- [Packaging](#)
- [Minimum_Quantity](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	3000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	

Box

Please approve our product specifications or to transact the approval sheet for product specifications before ordering.

Please read rating and !Cautions first.

Product specifications in this catalog are as of March 2010

Please make sure to read the Murata's [Product Policy](#) ,too.

All products and company names herein are trademarks or registered trademarks of their respective owners.

UP ^

| [Site Map](#) | [History](#) | [Terms of use](#) | [Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.