





REVISEMENTS						
P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
0		DRAWN	FJ00-1684-99	30SEP99	YF	KO



- ① Z面より7.5mmの位置で測定

② パワー回路(35極); FIG 1 参照

③ 回路番号; FIG 1 参照

4. 嵌合相手ハウジング型番
17P; 353027, 22P; 353028
24P; 353029, 31P; 1318682, 353826

5. 推奨取付ねじ: JIS B1115、B1122
タッピングねじ、なべ2種、呼び径3、
長さ6以下

6. ねじ締付トルク: 0.392N・m MAX

7. 取扱説明書 411-5931
- ① MEASURED AT THE SECTION 7.5mm FROM Z.

② POWER CIRCUITS (35); SEE FIG 1

③ CIRCUIT NUMBERS; SEE FIG 1

4. PART NO OF PLUG HOUSINGS TO BE MATED
17P; 353027, 22P; 353028, 24P; 353029
31P; 1318682, 353826

5. RECOMMENDED SCREW: PAN-HEADED, TYPE 2
TAPPING SCREW OF 3DIA X 6LEN(MAX)
(JIS B1115, B1122).

6. FASTENING TORQUE FOR SCREW: 0.392N・m MAX.

7. INSTRUCTION SHEET 411-5931




FIG 1 CIRCUIT NUMBERS (FOR POWER CIRCUIT)

NATURAL	PBT	TINE PLATE	1	⑤
PRE-TIN	COPPER ALLOY	TAB CONTACT(L)	38	④
PRE-TIN	COPPER ALLOY	TAB CONTACT(M)	47	③
PRE-TIN	COPPER ALLOY	TAB CONTACT(S)	40	②
NATURAL	PBT	CAP HOUSING	1	①
FINISH/COLOR	MATERIAL	NAME	QTY	ITEM NO
Y.FUJIIWALA 29SEP99 K.ODA 30SEP99 K.ODA 30SEP99				
PRODUCT SPEC 108-5673				
APPLICATION SPEC 取付適用規格				
WEIGHT	42.2g	SIZE	A2	00779
CUSTOMER DRAWING				

AMP 日本エー・エム・ピー株式会社
Kawasaki, Japan

040 II HIGH DENSITY CONNECTOR
125POS CAP HOUSING ASSY

SCALE 1-1 SHEET 1 OF 1 REV 0