

HELAVIA standard grommets DC (square edge)

in polychloroprene rubber (Neoprene)

(for technical properties see page D100)




HELAVIA

black
- 30 to + 90°C


HELAVIA standard grommets DC

type	article number	pack	measurements in mm				
			A	B	C	D	F
DC 51/70/15	0252 0213 010	100	5,1	7	11	1,5	3
DC 70/250/60	0252 0220 010	100	7	25	29	6	2
DC 90/110/10	0252 0201 010	100	9	11	16	1	3,25
DC 90/110/15	0252 0202 010	100	9	11	16	1,5	3,25
DC 90/110/20	0252 0203 010	100	9	11	16	2	3,25
DC 90/110/30	0252 0204 010	100	9	11	16	3	3,25
DC 90/110/40	0252 0212 010	100	9	11	16	4	3,25
DC 190/250/65	0252 0206 010	50	19	25	32	6,5	3
DC 190/250/135	0252 0207 010	50	19	25	32	13,5	3
DC 940/1010/30	0252 0211 010	25	94	101	109	3	5,5




Conical grommets series DC

type	article number	pack	measurements in mm				
			A	B	C	D	F1
DC 50/70/10	0252 0214 010	100	5	7	11	1	2




Conical grommets series DE

type	article number	pack	measurements in mm				
			A	B	C	D	F1
DE 65/100/10	0252 0299 010	100	6,5	10	16/14	1	3
DE 65/100/15	0252 0308 010	100	6,5	10	16/14	1,5	3
DE 65/100/20	0252 0304 010	100	6,5	10	16/14	2	3
DE 65/100/30	0252 0300 010	100	6,5	10	16/14	3	3



Elongated grommets series DH

type	article number	pack	measurements in mm				
			A	B	C	D	F1
DH 60/90/80	0252 0340 010	100	6	9	14	8	3
DH 80/115/50	0252 0321 010	100	8	11,5	16	5	4
DH 80/115/80	0252 0322 010	100	8	11,5	16	8	4
DH 80/115/160	0252 0323 010	100	8	11,5	16	16	4
DH 120/200/200	0252 0326 010	50	12	20	27,5	20	5
DH 130/200/150	0252 0328 010	100	13	20	28	15	5
DH 140/200/200	0252 0327 010	50	14	20	28	20	5
DH 250/310/330	0252 0320 010	25	25	31	37	33	5
DH 300/390/400	0252 0329 010	25	30	39	55	40	10



RS 136-6294

RS 136-6367

RS 136-6389

RS 136-6418

