

6

5



4

3

2

1

MATERIAL NUMBER	OLD PART NUMBER
130057-0003	ENSAM315



VOLTAGE RATING	125 VDC
AMPERAGE RATING	1.5 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
CATEGORY RATING	Cat 5

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT HOUSING	POLYCARBONATE	CLEAR
2	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
3	COUPLING NUT	ASA	BLACK
4	O-RING	VITON	BLACK
5	HOUSING	ASA	BLACK

CLARIFY THREAD DIMENSION
EC NO: IGC2017-0838
DRWN: MZIELINS 2017/03/08
CHKD: ---
APPR: BWOODMAN 2009/08/27
REV
A1

QUALITY SYMBOLS
$\nabla=0$
$\nabla C=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	$\pm---$	$\pm---$
3 PLACES	$\pm---$	$\pm---$
2 PLACES	$\pm---$	$\pm.01$
1 PLACE	± 0.3	$\pm---$
ANGULAR $\pm---$ °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
IN/MM	
DRAWN BY	DATE
YOU	2009/08/26
CHECKED BY	DATE
BWOODMAN	2009/08/31
APPROVED BY	DATE
JFMURPHY	2009/08/27
MATERIAL NO.	
SEE CHART	
SIZE	A

SCALE ---	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE RJ-LNXX ATTACHABLE FOR SOLID-CORE CABLE -----		
MOLEX INCORPORATED		
DOCUMENT NO. SD-130057-002		SHEET NO. 1 OF 1
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX D SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

6

5

4

3

2

1