







used for: D-SUB



JACK SCREW
INCL. WASHER AND O-RING

Shellsize	A	B	C	ØD	E	F	G ⁺¹ ₋₃	H	Cable Ø	Part NO.
1	40.76	25.0	22	24.6	51.0	22.0	77.0	44.0	5 - 10	165X14819XE
2	49.06	33.3	24	26.5	51.0	22.0	79.0	52.0	6 - 12	165X14829XE
3	62.80	47.04	24	26.5	59.5	22.0	87.5	52.0	6 - 12	165X14839XE
4	78.86	63.5	33	36.2	67.0	22.0	99.0	52.0	9 - 16	165X14849XE
5	76.46	61.1	42	47.0	67.0	24.8	107.0	52.0	13 - 20	165X14859XE

Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

- HOOD: PBT + GF, BLACK
- SCREWS: STAINLESS STEEL

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance		
2006	date	name
drawn	09.02.	Lehmenkühler
appd.	09.02.	Mickenbecker
norm		
d-old		
CONEC®		

scale: 1:1	
material: SEE NOTES	
title: WATER RESISTANT D-SUB HOOD 9-50pos. with jack screw	
dwg no: 16K1A1749	AutoCAD 2004
part no: SEE TABLE	DIN-A 3 sh: 1/1