

6.01533.00

Basic 250-24 W

## Compressor Basic 250-24 W



0153300S\_51.EPS

- Powerful, robust compressor for simple, commercial use
- Oil-lubricated piston condenser
- For single phase alternating current
- Working pressure can be regulated according to application by means of pressure reducer with manometer
- Good cold start feature thanks to push button with safety valve
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels for mobile use
- Testing not necessary before initial operation
- Additional manometer for displaying the tank pressure
- Rubber-coated handle for comfortable handling
- 10 years tank warranty against rusting

### Comparative technical values

|                                        |                       |
|----------------------------------------|-----------------------|
| Suction rate                           | 200 l/min             |
| Filling capacity                       | 110 l/min             |
| Effective delivery volume (at 80% max. | 95 l/min              |
| Maximum pressure                       | 8 bar                 |
| Rated input power                      | 1,5 kW                |
| Maximum speed                          | 2.850 /min            |
| Tank capacity                          | 24 l                  |
| Sound pressure level (LpA)             | 97 dB(A)              |
| Dimensions                             | 630 x 406<br>x 630 mm |
| Weight                                 | 27 kg                 |
| Cable length                           | 1,5 m                 |

### Scope of delivery

Universal quick-action coupling, Pull handle with rubber-coating