

REVISIONS

A	CO-83422
K D R	22 OCT 96

X34844

REPLACES

SR 12607

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK


MICRO SWITCH
 a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BE-1R242-A46




3X 8-32 UNC X (.219) BINDING
 HEAD TERMINAL SCREW AND
 LOCKWASHER (SEMS)

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 1.000 ± .002 CENTERS
 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 17 OZ MAX

DIFFERENTIAL FORCE - - - - - 5 OZ MAX

RELEASE FORCE - - - - - 10 OZ MIN

DIFFERENTIAL TRAVEL - - .0015 - .0040

OVERTRAVEL - - - - - .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

25-A-125, 250, 480 VAC 1 HP-125 VAC;
 2 HP-250 OR 480 VAC; PILOT DUTY
 750 VA-480 VAC, MAX; 60/75°C (Cu)



SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT .063 LB

FORMTEK

DRAWN

K D R 22 OCT 96

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BE-1R242-A46](#)