




CONFIDENTIAL

VERTRAULICH


THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

1	2	3	4
recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
	0.75 to 1	30 +0.1	22.2 +0.2
	>1 to 1.5	30.2 +0.1	22.2 +0.2
	>1.5 to 3	30.4 +0.1	22.2 +0.2




DPST
Total travel 4±0.4
Suitable for appliances of class II



Marking
MARQUARDT®
1661.
16(4)/250~ T85/55
R 84

12 A 125-250 V AC
1/6 HP 125V AC
1/2 HP 250 V AC
R 84



Code of manufacture: place/year/week

-	-	-	1661.0220-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle ± 2 °	Sheet 01	
	Edge tolerance	Ident.	Document number
		K	16610220
		Appliance Switch	
f	137245	2021-04-30	JOSHIO
e	32547	2002-05-23	SIG
d	28075	1999-10-12	MUT
c	26325	1998-09-30	BB
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		System NX V1872	Replacement of
		Zg.gl.Nr.v.30.09.1998	
		MARQUARDT	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Marquardt:

<u>1661.0220</u>	<u>1667.0102</u>	<u>1660.5853</u>	<u>1661.0120</u>	<u>1662.0301</u>	<u>1663.0201</u>	<u>1660.5205</u>	<u>1665.5504</u>	<u>1660.0223</u>	<u>1660.0203</u>
<u>1660.5201</u>	<u>1665.3101</u>	<u>1660.0407</u>	<u>1662.0102</u>	<u>1660.5202</u>	<u>1660.8204</u>	<u>1661.5201</u>	<u>1662.0103</u>	<u>1662.0106</u>	<u>1667.0104</u>