


PCB Modular Jack

154-7641PCB

KOBICONN

PCB Modular Jack



Dimensions: mm

SPECIFICATIONS	
Type:	8P8C modular phone w/PCB leads
Housing:	PBT added 15% glass fiber
Color:	gray
Western Electric type:	641PCB
USOC type:	RJ45
Contact:	6μ gold plated phosphor bronze alloy
Insulation resistance:	500MΩ min.
Contact resistance:	10mΩ max. per contact
Dielectric withstanding voltage:	1000V RMS 60Hz
Current rating:	1.5A
Insertion force:	900g
Retention strength:	5kgs between jack and plug

Date Last Revised: 6-25-12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300627

154-7641PCB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-7641PCB](#)