






1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE STAMPED M24308/2-292F
 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 OR AMP # 205090
- AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
UL/CSA DESIGNATION STAMPED IN THIS AREA.

OBSOLETE

BRASS
STEEL PER
ASTM-A-109

205416-2
205416-1
PART NO

SHELL MAT'L

AMP INCORPORATED
MILWAUKEE, WIS. 53211

NAME
AMP
HI-DENSITY RCPT. FOR SOCKET CONTACTS
HI-DENSITY "HDM-20" CONNECTOR
SIZE 1 (9 POSN) SERIES 109
WITH FLOAT BUSHINGS

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 1. DIMS ±.005 2. PLG DEC ±.005 3. PLG DEC ±.005 4. ANGLES ±0°30'	DR 12-9-87 C.C. THOMAS CHK 12-10-87 FC BALLEW III APPD 12-10-87 FC BALLEW III APPD 12-10-87 DJM	SIZE C 00779 DRAWING NO 205416 SHEET 1 OF 1
FINISH SEE CALLOUTS	APPLICATION SPEC	WEIGHT
SEE CALLOUTS		