

ROITHNER LASERTECHNIK

A-1040 WIEN, FLEISCHMANNGASSE 9

TEL: +43 -1- 586 52 43 FAX: +43 -1- 586 41 43

e-mail: office@roithner-laser.com http://www.roithner-laser.com

RLT6850G

TECHNICAL DATA



High Power Visible Wavelength Laserdiode

Structure: **AlGaInP**, index guided, single transverse mode

Lasing wavelength: **685 nm typ.**


Max. optical power: **50 mW cw**

Package: **9 mm**




NOTE!
LASERDIODE
MUST BE COOLED!

PIN CONNECTION:



- 1) Laser diode anode
- 2) Laser diode cathode and photodiode anode
- 3) Photodiode cathode



Maximum Ratings (Tc=25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Optical Output Power cw	P_o	60	mW
LD Reverse Voltage	$V_{R(LD)}$	2	V
PD Reverse Voltage	$V_{R(PD)}$	30	V
Operation Case Temperature	T_c	-10 .. +60	°C
Storage Temperature	T_{STG}	-10 .. +100	°C

Optical-Electrical Characteristics (Tc = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Optical Output Power	P_o	kink free		50		mW
Threshold Current	I_{th}	cw		35	60	mA
Operation Current	I_{op}	$P_o = 50$ mW		100	140	mA
Operating Voltage	V_{op}	$P_o = 50$ mW	2.0	2.7	3.0	V
Lasing Wavelength	λ_p	$P_o = 50$ mW	670	685	700	nm
Beam Divergence	$\theta_{//}$	$P_o = 50$ mW	7	9.5	12	°
Beam Divergence	$\theta_{\perp}$	$P_o = 50$ mW	16	20	25	°
Slope efficiency	η	$P_o = 50$ mW		0.75		mW/mA
Monitor Current	I_m	$P_o = 50$ mW, $V_r = 5$ V	0.05	0.3	2.5	mA