


Female Header Micro Match SMD 1.27 mm

Series

374



Rated current	1,5 A
Rated voltage	230 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch
1,27


termination



max.
pincount
026


Variation

Without locking feature



1

With locking feature



2

Plating:
T = Sn

Packaging:
R = Reel
T = Tube

Cap:
0 = Without cap
1 = With cap

Variation (1,2)

No. of contacts

Plating contact

Packaging (R,T)

Cap (0,1)



www.mpe-connector.de

C0130319 V6

Order code:

374-?-?-?-0-NTX-K??

[illegible]