


シリコン整流素子 Silicon Rectifier Diodes

品名	色別	Io (A)	VRM (V)	IFSM (A)	VF (max.) (V)	IR (max.) (μA)	外形図
DIR20	赤	0.35	200	10	1.65	5	1
DIR60	青		600				
DIR80	緑		800				
DIR100	銀		1000				
DIR150	金	0.75	1500	30	1.05	5	4
DIR20Z	赤		200				
DIR40Z	黄	1	400	30	1.1	10	1
DIV20	赤		200				
DIV40	黄		400				
DIV60	青	1.7	600	60	1.05	10	1
S2V10	茶		100				
S2V20	赤		200				
S2V40	黄		400				
S2V60	青	3.5	600	120	1.05	10	1
S3V10	茶		100				
S3V20	赤		200				
S3V40	黄		400				
S3V60	青	3.5	600	120	1.05	10	4
S3V60Z	青		600				

シリコン整流スタック・ブリッジ Bridge type


品名	Io (A)	VRM (V)	IFSM (A)	VF (max.) (V)	IR (max.) (μA)	外形図
SIYB10	0.4	100	30	1.05	10	2
SIYB20		200				
SIYB40		400				
SIYB60		600				
SIWB(A) 10	1	100	30	1.05	10	3
SIWB(A) 20		200				
SIWB(A) 40		400				
SIWB(A) 60		600				
SIVB10	1	100	30	1.05	10	5
SIVB20		200				
SIVB40		400				
SIVB60		600				
SIVB20Z	1	200	30	1.05	10	5
SIVB40Z		400				
SIVB60Z		600				
SIRBA10	1	100	30	1.05	10	6
SIRBA20		200				
SIRBA40		400				
SIRBA60		600				
SIRBA80	1	800	30	1.05	10	6
SIRBA20Z		200				
SIRBA40Z	1	400	30	1.05	10	6
S2VB10	2	100	40	1.05	10	7
S2VB20		200				
S2VB40		400				
S2VB60		600				
S3WB10	2.3	100	120	1.05	10	8
S3WB20		200				
S3WB40		400				
S3WB60		600				
S4VB10	4	100	80	1.05	10	9
S4VB20		200				
S4VB40		400				
S4VB60		600				
D5SB10	5	100	170	1.05	10	10
D5SB20		200				
D5SB40		400				
D5SB60		600				
S5VB10	6	100	200	1.05	10	11
S5VB20		200				
S5VB40		400				
S5VB60		600				

図1



形名	A	B	C
D1R D1V D1K	5.5	2.7	0.6
S1SM	5.5	2.7	0.8
S2V K1V S2K	7.5	4.8	1
S3V S3SM S3K	7.5	4.8	1.4

図4



形名	A	B	C
D1RZ	5.5	2.7	0.6
S3V60Z	7.5	4.8	1.4

図2




図3




図5




図6




図7




図8




図9




図10




図11




図12




図13

