

プラスチック防水ハンドル

PLASTIC WATERPROOF HANDLES


AP-140
プラスチック製

特徴 Feature

- 防水タイプ (Oリング・シートパッキン使用)
- 亜鉛合金がインサートされております。
- 耐酸・耐絶縁性を必要とする扉に最適
- 左右兼用型
- Waterproof (using O-ring and sheet packing)
- Zinc alloy is inserted.
- Suitable for doors that require acid-resistance and insulation.
- For both left-hand and right-hand use.

- 仕様**
- 材質: ABS樹脂
 - 標準色: N7 (グレー) 5Y7/1 (アイボリー)
 - 鍵番号: 2001
 - 付属品: 大ナット・ビスセット (止め金用)・キー2本
- 用途**
- 隧道用配分電盤
 - 標準在庫品
- 備考**
- ダブルOリングの完全防水タイプも製作致します。
 - 止め金は646～650ページの中からお選びください。
 - マスターシステムの組込みが可能です。お問合せください。
 - 常温でご使用ください。
 - 施錠錠は錠前の構造上、鍵を押しながら回してください。
 - 本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。
 - 緩み防止剤等、溶剤を使用する際は十分に検証を行ってください。

- Specifications**
- Material: ABS resin
 - Standard color: N7: Gray. 5Y7/1: Ivory
 - Key No.: 2001
 - Accessories: Two keys, large nut and screws (for stopper plate)


- Specific use**
- Tunnel power/distribution boards
- Remarks**
- Double-O-ring-fully-waterproof type is available.
 - Select stopper plate on page 646 to 650.
 - Incorporating master system is possible. Consult us.
 - Use this product in normal temperatures.
 - Due to the structure of the lock, the key must be pushed in as it is turned in order to release the lock.
 - It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.
 - Be sure to test adequately when using a solvent such as thread-locking fluid.




AP-140-1-1
N7

AP-140-2-1
5Y7/1

キーNo.2001
Key



パネル穴明け寸法 Panel drilling dimensions



商品番号 Product No.	RoHS	CAD	備考 Remarks	L1	L2	W1	W2	W3	W4	H1	H2	H3	H4	H5	P	φD1	φD2	φD3	(M)	最大適用板厚 Max. applicable panel thickness	製品質量 (g) Mass	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity 単価 Price
AP-140-1-1-N7	●	2D/3D	鍵付き With lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	00314	¥2,500	10個～ ¥2,400
AP-140-1-1-5Y7/1	●	2D/3D	鍵付き With lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	01038	¥2,500	10個～ ¥2,400
AP-140-1-2-N7	●	3D	鍵なし Without lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	00316	¥1,700	10個～ ¥1,632
AP-140-1-2-5Y7/1	●	3D	鍵なし Without lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	01039	¥1,700	10個～ ¥1,632
AP-140-2-1-N7	●	2D/3D	鍵付き With lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	00318	¥2,250	20個～ ¥2,160
AP-140-2-1-5Y7/1	●	2D/3D	鍵付き With lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	01040	¥2,250	20個～ ¥2,160
AP-140-2-2-N7	●	3D	鍵なし Without lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	00320	¥1,650	20個～ ¥1,584
AP-140-2-2-5Y7/1	●	3D	鍵なし Without lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	01041	¥1,650	20個～ ¥1,584

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

ハンドル・取手
つまみ・周辺機器



A

クレモン

ローラー
締り

特装密閉
ハンドル

フリーザー
密閉

平面
スイング

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L-SHAPED HANDLES
L 型
ハンドル
T 型
ハンドル
丸型
小型
押ボタン

取手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ

18.01

TAKIGEN
総合 24

497