


NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corporation (2) must be returned upon request; and (3) are confidential and are not to be disclosed to any person other than those to whom they are given by Amphenol Corporation. The furnishing of these drawings, specifications, or other data by Amphenol Corporation, or by any other person, to anyone for any purpose is not to be regarded by implication or otherwise as in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications or other data.



AMPHENOL NO.	CATALOGUE NO.	CABLE	FITTING	CONNECTOR	THREAD	A	B	ADAPTER	CLAMP * LESS 2 WASH.	BUSHING	WASHER ONLY
97-67-3	10-825923-3	5/32	3		1/2-28	1	2 1/32		AN-3057-3	9779-31	9776-3
97-67-12-3	10-825923-121	5/32		85-10S	1/2-28	1 1/32	2 1/32	3055-10-3	AN-3057-3	9779-31	9776-3
97-67-4	-4	7/32	4		1/2-28	1	2 1/32		AN-3057-4	9779-41	9776-4
97-67-12-4	-123	7/32		85-10S	1/2-28	1 1/32	2 1/32	3055-10-4	AN-3057-4	9779-41	9776-4
97-67-14-4	-141	7/32		12S-12	5/8-24	1 1/32	2 1/32	3055-12-4	AN-3057-4	9779-41	9776-4
97-67-16-4	-161	7/32		14S-14	3/4-20	1 1/32	2 1/32	3055-14-4	AN-3057-4	9779-41	9776-4
97-67-6	-6	1 1/32	6		1/2-28	1	2 1/32		AN-3057-6	9779-61	9776-6
97-67-14-6	-142	1 1/32		10SL	5/8-24	1 1/32	2 1/32	3055-12-6	AN-3057-6	9779-61	9776-6
97-67-16-6	-162	1 1/32		14S-14	3/4-20	1 1/32	2 1/32	3055-14-6	AN-3057-6	9779-61	9776-6
97-67-18-6	-181	1 1/32		16S-16	7/8-20	1 1/32	2 1/32	3055-16-6	AN-3057-6	9779-61	9776-6
97-67-8	-8	7/16	8		1/2-28	1 1/32	2 1/32		AN-3057-8	9779-81	9776-8
97-67-16-8	-163	7/16		16S-16	7/8-20	1 1/32	2 1/32	3055-16-8	AN-3057-8	9779-81	9776-8
97-67-18-8	-182	7/16		18	1-20	1 1/32	2 1/32	3055-18-8	AN-3057-8	9779-81	9776-8
97-67-22-8	-221	7/16		20-22	1 1/16-18	1 1/32	2 1/32	3055-22-8	AN-3057-8	9779-81	9776-8
97-67-10	-10	9/16	10		1-20	1 1/8	1 1/8		AN-3057-10	9779-101	9776-10
97-67-18-10	-183	9/16		18	1-20	1 1/8	1 1/8	3055-18-10	AN-3057-10	9779-101	9776-10
97-67-22-10	-222	9/16		20-22	1 3/16-18	1 1/8	1 1/8	3055-22-10	AN-3057-10	9779-101	9776-10
97-67-28-10	-281	9/16		24-28	1 1/16-18	1 1/8	1 1/8	3055-28-10	AN-3057-10	9779-101	9776-10
97-67-12	-12	1 1/16	12		1 3/16-18	1 1/8	1 1/8		AN-3057-12	9779-121	9776-12
97-67-22-12	-223	1 1/16		20-22	1 3/16-18	1 1/8	1 1/8	3055-22-12	AN-3057-12	9779-121	9776-12
97-67-28-12	-282	1 1/16		24-28	1 1/16-18	1 1/8	1 1/8	3055-28-12	AN-3057-12	9779-121	9776-12
97-67-32-12	-321	1 1/16		32	1 3/4-18	1 1/2	1 1/2	3055-32-12	AN-3057-12	9779-121	9776-12
97-67-16	-16	2 1/32	16		1 1/16-18	1 1/8	1 1/8		AN-3057-16	9779-161	9776-16
97-67-28-16	-283	2 1/32		24-28	1 1/16-18	1 1/8	1 1/8	3055-28-16	AN-3057-16	9779-161	9776-16
97-67-32-16	-322	2 1/32		32	1 3/4-18	1 1/2	1 1/2	3055-32-16	AN-3057-16	9779-161	9776-16
97-67-36-16	-361	2 1/32		36	2-18	1 3/4	1 3/4	3055-36-16	AN-3057-16	9779-161	9776-16
97-67-32-20	-20	1 1/32	20		1 3/4-18	1 1/2	1 1/2		AN-3057-20	9779-201	9776-20
97-67-32-20	-323	1 1/32		32	1 3/4-18	1 1/2	1 1/2	3055-32-20	AN-3057-20	9779-201	9776-20
97-67-32-20	-362	1 1/32		36	2-18	1 3/4	1 3/4	3055-36-20	AN-3057-20	9779-201	9776-20
97-67-32-20	-401	1 1/32		40	2 1/4-16	2 1/8	2 1/8	3055-40-20	AN-3057-20	9779-201	9776-20
97-67-24	-24	1 1/16	24		2-18	1 1/2	1 1/2		AN-3057-24	9779-241	9776-24
97-67-44	-44	1 1/16	44		2 1/4-16	2 1/8	2 1/8		AN-3057-24	9779-241	9776-24
97-67-44	-44	1 1/16	44		2 1/2-16	2 1/8	2 1/8		AN-3057-24	9779-241	9776-24
97-67-28	-28	1 1/8	28		2 1/4-16	1 1/2	1 1/2		AN-3057-28	9779-281	9776-28
97-67-28	-28	1 1/8	28		3-16	2 1/8	2 1/8		AN-3057-28	9779-281	9776-28
97-67-32	-32	1 5/8	32		2 1/2-16	1 1/2	1 1/2		AN-3057-32	9779-321	9776-32
97-67-32	-32	1 5/8	32		2 1/2-16	1 1/2	1 1/2		AN-3057-32	9779-321	9776-32
97-67-40	-40	2	40		3-16	1 5/8	1 5/8		AN-3057-40	9779-401	9776-40

IDENTIFY PACKAGE WITH "AMPHENOL" AND AMPHENOL PART NUMBER
EXAMPLE:

97-67-14-4

9) ADDED TO NUMBER INDICATES CLAMP LESS TWO WASHERS.
SS(1) 10-825925-XX & LESS (1) 10-825924-XX WASHER.

TE

UNLESS OTHERWISE SPECIFIED

LINEAR DIMENSIONS ARE IN INCHES
TOLERANCES: .XXX ± .010,
.XX ± .03, .X ± .1, ANGLES ± 2°
OTHER STANDARDS PER 9-3800
AND DOD-D-1000.

DRAWN HOFRICHTER		DATE 8-12-65
CHECKED J. H. L. X.		8-16-65
APPROVED G. H.		8-16-65
ENGINEERING RELEASE		
No. 11		7-23-43
INDUSTRIAL ENGRG APPD.		
DESIGN ACTIVITY APPD.		
EXPERIMENTAL NO.		
FINAL ASSEMBLY		
NEXT USED ON		
MATERIAL		
FINISH		
TITLE		WATERTIGHT CLAMP ASSEMBLY
SIZE	FSCM NO.	REV
C	77820	P
SCALE	WT. EST.	ACT.
		SHEET
		OF

REVISIONS

SYM	ZONE	DESCRIPTION	DATE	APPROVED
G		REVISED & REDRAWN CN 27230	8-12-65	J.H.
H	B4	P/N 9767-44-24 OBSOLETE. C.N. 29594 J.B.	11-7-67	J.H.
J	C-4	P/N 9767-10-3 OBSOLETE CN30051 B.D.	8-12-68	J.H.
K		CANCEL SIZES 9767-40-20 & 9760-40-24 PER ECN #43015-A	11-12-77	J.H.
L		CANCELLED 9767-36-24 CN 44261	11-6-81	J.H.
M		ECO DOCUMENT NOS. INCORPORATED CHANGED FSCM NO. TO 77820 ECN: 75005-342	9/18/87	J.H.
N		(CLII) SEE CHANGE NOTICE ECN: 81193	1-16-96	J.H.
P		(CLII) SEE ECN: 81773	7-22-96	J.H.

TAB.