




FCI 4-Way APEX 2.8 mm Connection System


FEMALE



Sealed Assembly

Unsealed Assembly

MALE



Sealed Assembly

Unsealed Assembly

INDEX TYPE	HOUSING COLOR	SEALED/ UNSEALED	FEMALE ASSEMBLY PART NUMBER	MALE ASSEMBLY PART NUMBER	TEMPERATURE RATING OF MATERIAL	WIRE INSULATION RANGE PER CAVITY (mm)
A	BLK	SEALED	54200409	54200413	-40°C to +125°C	1.70 – 2.77
A	BLK	UNSEALED	54200400	54200405	-40°C to +125°C	1.50 – 4.09
B	LT GREY	SEALED	54200410	54200414	-40°C to +125°C	1.70 – 2.77
C	DK GREY	SEALED	54200411	54200415	-40°C to +125°C	1.70 – 2.77
C	DK GREY	UNSEALED	54200403	54200407	-40°C to +125°C	1.50 – 4.09
D	NATURAL	SEALED	54200412	54200416	-40°C to +125°C	1.70 – 2.77
D	NATURAL	UNSEALED	54200404	54200408	-40°C to +125°C	1.50 – 4.09
B	LT GREY	SEALED	54000450*	—	SEAL W/O HOLES	USED AS CAP
A	BLACK	SEALED	—	54200427*	SEAL W/O HOLES	USED AS CAP

* Plug for same index (A) mating part.

Note: Female part numbers with the N suffix are without CPA latch.

3.35mm wire diameter sealing is available in select configurations. Consult sales drawing.

Additional configurations available. Please consult sales drawing.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[54200413](#) [54200414](#) [54200413-B](#) [54200414-B](#)