


A range of plugs that are available in two pin styles; hollow or solid. The plug incorporates a unique ‘T’ slot design which allows the interconnection between non-standard sockets. A rigid acetal cap is offered in two colours, red or black.

- Ground contact with unique ‘T’ shape slots for maximum contact area.
- Internal cable clamp for secure cable connection.
- Maximum cable size 4.1mm.
- Two colours available, black or red.

Dimensions



Deltron Part No	
413-000	414-0000
415-0000	416-0000

Material	:Brass,
Centre contact	Silver plated
Ground contact	:Brass,
Insulation	Nickel plated
Cable clamp	:Noryl, SE1 UL94 V-1
Spring	:Brass,
Body	Silver plated
Cap	:Brass,
	Nickel plated
	:Brass,
	Nickel plated
	:Acetal, UL 94 HB
Ratings	:5 Amps at 200 Vdc
	150 Vac max.
Insulation resistance	: 100M Ω at 500 Vdc

HOLLOW PIN	BLACK	RED
NICKEL	413-0100	413-0500
GOLD	414-0100	414-0500

SOLID PIN	BLACK	RED
NICKEL	415-0100	415-0500
GOLD	416-0100	416-0500

CONVERTED FROM PS0466 ISS4 (01.07.94) IN JAN 2003

DrgnNo 413-414-415-416	TITLE STANDARD PHONO PLUG WITH INSULATED HOUSING	ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES
------------------------	--	---



ES
S1

4

GENERAL SPECIFICATION
FOR 413-414-415-416

CUSTOMER

Aprvd Date 03/02/03

Aprvd By MC

Drwn by BS

Scale: NTS

Sheet 1 / 1

