


Cable Mounting & Routing



Page E-2



Page E-2



Page E-3




Page E-3



Page E-4



Page E-4




Page E-4



Page E-5



Page E-5



Page E-6



Page E-7



Page E-7



Page E-8



Page E-8



Page E-8



Page E-9



Page E-9



Page E-10




Page E-10



Page E-11




Page E-11



Page E-12




Page E-12




Page E-13




Page E-13




Page E-14




Page E-14



Page E-14



Page E-15



Page E-15



Page E-16



Page E-16




Page E-17




Page E-17




Page E-18



Page E-18



Page E-19




Page E-19



Page E-20



Page E-20



Page E-21




Page E-21



Page E-22




Page E-22




Page E-22




Page E-23




Page E-23




Page E-23



Page E-24



Page E-24



Page E-24



Page E-25



Page E-25



Page E-25



Page E-26



Page E-26




Page E-26



Page E-27



Page E-27



Page E-28



Page E-28



Page E-28




Page E-29



Page E-29

Navigation help: Click on page No. to jump to page.
Or enter chapter page No. in Adobe Reader (e.g. „E-14“).
Use „last view“ button in Adobe Reader to return to this index.

Cable Mounting & Routing



Page E-30



Page E-30



Page E-30



Page E-31



Page E-31




Page E-32




Page E-32




Page E-33



Page E-33




Page E-34



Page E-35



Page E-35



Page E-37



Page E-38



Page E-38



Page E-38



Page E-39



Page E-39



Page E-39



Page E-40



Page E-40



Page E-41



Page E-42




Page E-42




Page E-43



Page E-43



Page E-44



Page E-45



Page E-46



Page E-47


Navigation help: Click on page No. to jump to page.
Or enter chapter page No. in Adobe Reader (e.g. „E-34“).
Use „last view“ button in Adobe Reader to return to this index.

• Cable Mounting & Routing




RoHS compliant

Flat Cable Mount




GDD

Material:	PVC
Flame class:	94 V-2
Color:	Grey
Std. Package:	250 / 500 pcs.




Part No.	A mm	Package
GDD-15	15.0	500
GDD-20	20.0	
GDD-25	25.0	250

Flat Cable Mount



GDO

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.




Part No.	A mm
GDO-15	15.0
GDO-20	20.0
GDO-25	25.4



RoHS compliant


Mini Flat Cable Clamp



- Application cable: width, max: 16(.630)
thickness, max: 2.7(.106)
- Height when fixed: 9(.354)
- Width: 10(.394)


Part No.	Package
LFC-16N-0	1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.



LFC-16N-0

Mini Flat Cable Clamp



Part No.	A mm	B mm	C mm	Applicable cable		Height when fixed
				width	thickness	
LFC-20W	30.4	25.6	10.0	21	1.2	7.2
LFC-27W	37.4	32.6	14.0	28		
LFC-30N-O	40.0	35.0		30	1.0	7.0

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.



LFC




RoHS compliant

Flat Cable Clamp



GDF

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 / 200 pcs.




Part No.	A mm	B mm	C mm	D mm	Package
GDF-1	31.5	40.7	2.0	6.8	200
GDF-2	52.0	61.2	2.1	6.9	100

Flat Cable Clamp




GDF-3

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




Part No.	Package
GDF-3	100

Flat Cable Clamp




GDF

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.



SUITABLE CABLE: 40 PIN



Part No.	Package
GDF-40	100



SUITABLE CABLE: 30 PIN

Part No.	Package
GDF-30	100

Flat Cable Clamp




GDB

Part No.	A mm	B mm	C mm	D mm	Package
GDB-1	19.7	77.6	64.0	12.8	50
GDB-2	19.0	53.5	40.0	11.2	100
GDB-3		45.8	32.0		200
GDB-5	19.8	45.4	31.8	18.0	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	50 / 100 / 200 pcs.

Flat Cable Clamp



GDC

Part No.	A mm	B mm	C mm	Suitable cable	Package
GDC-40	53.8	65.0	10.2	40 PIN	200
GDC-50	64.5	77.0	10.0	50 PIN	100


Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 / 200 pcs.




RoHS compliant

Flat Cable Clamp


■ Snap Type (FCS)




■ Snap Type (FCSS)



■ Snap Type (FCN)



■ Cushion Pad



Snap-type (FCS)

Part No.	Cable width	Cable thickness	A mm	B mm	C mm	D mm	E mm	P mm
FCS-3010	31.0	6.5	20.0	45.5	15.0	9.0	4.0	33.0
FCS-3015		13.0				15.4		
FCS-6010	63.0	6.5		77.0		9.0		64.5
FCS-6015		13.0				15.4		

Adhesive-type (FCN)

Part No.	Cable width	Cable thickness	A mm	B mm	C mm	D mm	E mm
FCN-3010	31.0	6.5	20.0	45.5	15.0	9.0	3.8
FCN 3015		13.0				15.4	
FCN-6010	63.0	6.5		77.0		9.0	
FCN-6015		13.0				15.4	
FCN-6020		19.0				21.1	

Snap-type (FCSS)

Part No.	Cable width	Cable thickness	A mm	B mm	C mm	D mm
FCSS-6010	63.0	6.5	20.0	77.0	15.0	8.9
FCSS-6015		13.0				15.3


Cushion Pad

Part No.	H mm	W mm	D mm	Fits FCS/FCN
S-630	6	30	13	FCS. FCN-3010
S-1330	13			FCS. FCN-3015
S-660	6	60		FCS. FCN-6010
S-1360	13			FCS, FCN-6015
S-2060	20			FCN-6020

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Natural
 Std. Package: 100 pcs.

FC

Flat Cable Clamp




FCS

Part No.	Cable width	Cable thickness	A mm	B mm	C mm	D mm	P mm	W mm
FCS-25P	32.0	2.6	10	47	23	32	21	19
FCS-50P	63.5	7.0	14		50	64	52	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Flat Cable Clamp



FCN

Part No.	Cable width	Cable thickness	A mm	B mm	C mm	D mm	W mm
FCN-25P	32.0	2.6	12	47	23	32	19
FCN-50P	63.5	7.0	16	79	50	64	
FCN-60M	77.0	16.0	26	90	76	78.5	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




RoHS compliant

Flat Cable Clamp



GDU




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	50 pcs.

Part No.	A mm	B mm	C mm
GDU-2	53.5	40.0	30.0
GDU-3	45.5	32.0	25.0

Flat Cable Clamp



GDU-4




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Part No.	Package
GDU-4	100

Flat Cable Clamp




GDU-5



Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	50 pcs.

Part No.	Package
GDU-5	50

Flat Cable Clamp



FCW

Part No.	A mm	B mm	C mm	D mm	E mm	F mm
FCW-26	26	35.5	18	29.5	14.5	-
FCW-52	52	61.5	44	55.5	8.45	38.1

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Grey
Std. Package:	100 pcs.




RoHS compliant

Flat Cable Clamp



GDI-30

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Grey
Std. Package:	100 pcs.




Part No.	Package
GDI-30	100

Flat Cable Clamp



GDI




Part No.	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm
GDI-50	53.0	39.0	64.6	57.3	8.3	4.1	8.8	3.7
GDI-80	78.93	38.7	90.6	82.3	12.3	6.3	7.6	3.8

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Grey
Std. Package:	50 pcs.




RoHS compliant

Cable Routing




Part No.	A mm
UIF-12	12.7
UIF-17	16.8
UIF-25	25.0
UIF-37	36.8

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.




UIF

Cable Routing



Part No.	Package
UIF-9	500

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.




UIF-9




RoHS compliant

Cable Routing



UIB




CHASSIS $\varnothing 4.8\sim 5.0$ THICKNESS 1.0~3.2


Part No.	A mm	B mm	C mm	D mm	Closec	Package
UIB-1	33.8	3.1	7.1	10.6	6.1	1000
UIB-2	51.0	20.0				500
UIB-3	66.0	35.3				
UIB-4	39.6	2.8	10.8		9.8	1000
UIB-5	56.8	20.0				500
UIB-6	71.5	35.2				
UIB-7	42.0	3.0	15.0		13.8	1000
UIB-8	59.3	20.4				500
UIB-9	74.7	35.8				
UIB-10	63.5	16.2	20.0		18.4	
UIB-11	56.8	3.0	24.3	9.8	22.3	
UIB-12	53.1	15.3	11.0	10.8	9.7	
UIB-14	55.3	5.0	20.3	10.6	18.7	
UIB-15	43.8	10.5	8.0		6.8	
UIB-16	34.7	5.6	8.8	10.0	7.0	

Material: Nylon 66 (UL)
Flame class: 94 V-2
Color: Natural
Std. Package: 500 / 1000 pcs.

Cable Routing




LM




Part No.	A mm	B mm	C mm	D mm	Closed	Package
LM-1	31.9	20.0	20.0	15.0	13.8	250
LM-2	26.2		14.0	9.2	8.5	500
LM-2L	27.9	25.0	13.0	9.4	8.2	
LM-3	28.2	21.0	19.0	11.1	10.0	
LM-5	56.2	38.0	20.0	36.0	34.0	100
LM-6	27.6	10.0	19.8	6.6	5.8	
LM-7	21.9	20.0	13.0	8.5	7.2	500
LM-16	37.0	25.0	13.0	18.0	17.0	250
LM-19	39.0			21.0	20.0	
LM-22	41.0			24.0	23.0	

Material: Nylon 66 (UL)
Flame class: 94 V-2
Color: Natural
Std. Package: 100 / 250 / 500 pcs.


Cable Routing



Part No.	Package
Z 2L-7	500




Part No.	Package
Z 2L-8	500




Z 2L

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.

Cable Routing



Part No.	A mm	D mm	Closed	Package
UM-1	17.8	5.1	4.0	1000
UM-2	23.8	8.3	7.3	
UM-3A	27.5	11.5	10.0	
UM-4	30.4	15.4	13.8	
UM-5	35.0	18.8	17.2	500
UM-6	41.4	25.8	24.2	
UM-7	42.0	22.0	19.5	
UM-8	16.5	5.6	5.0	
UM-13	32.5	13.2	11.5	
UM-28	55.5	29.0	26.8	




UM

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 / 1000 pcs.





RoHS compliant

Cable Clamp




XDT 1

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.





Part No.	Package
XDT 1	500

Cable Clamp




GDQ

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.





Part No.	A mm	Double adhesive tape
GDQ-22	25.2	THICKNESS:1.1mm
GDQ-22SN	24.2	(no)

Cable Clamp





GDQ-25

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.



Part No.	Package
GDQ-25	500

Cable Clamp





GXT

Part No.	A mm	B mm	C mm	D mm	Package
GXT-1	21.0	19.0	9.2	8.2	500
GXT-2	25.0	20.0	12.0	9.0	250
GXT-3	25.0	19.7	12.1	10.6	
GXT-4	29.0	20.0	14.0	12.6	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	250 / 500 pcs.

Cable Clamp



BXD


Part No.	A mm	B mm	C mm	D mm	Package
BXD-1	24.8	18.8	10.2	7.9-10.3	250
BXD-2	25.4	15.0	10.0	11.0-13.3	
BXD-2A	30.2	15.0	10.0	11.9-14.3	
BXD-3	34.4	18.8	12.7	14.7-19.1	100
BXD-4	36.0	19.0	12.7	18.0-22.0	
BXD-5	39.8	19.8	13.0	22.0-26.5	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 / 250 pcs.




RoHS compliant

Cable Clamp




CKN




Part No.	A mm	B mm	C mm	D mm	E mm	F mm	Bundle diameter	Package
CKN-05	20.5	17.5	3.0	8.5	10.8	9.8	5.4	100
CKN-07	17.5	25.5	3.2	9.8	12.1	11.0	6.5	
CKN-10	21.0	30.0	3.5	12.0	14.3	15.0	10.0	
CKN-13	24.0	30.0	3.5	14.0	16.3	21.0	14.4	
CKN-16	25.5	36.0	4.0	16.0	18.3	24.0	17.4	
CKN-20	30.0	40.0	4.0	18.0	20.3	26.0	20.0	
CKN-28	42.5	55.5	4.6	24.2	27.4	34.0	29.0	20
CKN-38	75.8	55.5	5.1	29.5	33.4	45.0	38.0	

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Grey
 Std. Package: 20 / 100 pcs.

Clamp with Cushion Pad




CKN



Part No.	A mm	B mm	C mm	D mm	E mm	F mm	Bundle diameter
CKN-10SP	21.0	30.0	3.5	12.0	14.3	15.0	6 - 8
CKN-13SP	24.0			14.0	16.3	21.0	7 - 10
CKN-16SP	25.5	36.0	4.0	16.0	18.3	24.0	9 - 13
CKN-20SP	30.0	40.0	4.0	18.0	20.3	26.0	10 - 14

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Grey
 Std. Package: 100 pcs.

Adjustable Clamp




AC

Part No.	Package
AC-13	100

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Black
Std. Package:	100 pcs.

Cable Clamp



Hole Dia: 6.4mm Panel Thickness: 0.5-4.1mm



CKS


Part No.	A mm	B mm	C mm	D mm	E mm	F mm	Bundle diameter
CKS-05-L	13.8	23.2	20.5	8.5	7.7	5.0	5.4
CKS-05-H		22.3			9.5		
CKS-07-L	15.1	25.0	22.9	9.8	7.7	5.0	6.2
CKS-07-H		24.7			9.5		
CKS-10-L	17.3	28.4	27.4	12.0	7.7	5.0	9.8
CKS-10-H		29.2			9.5		
CKS-13-1	19.3	32.0	33.3	14.0	7.7	5.0	14.4
CKS-13-H		35.1			9.5		
CKS-16-L	21.3	35.0	33.9	16.0	7.7	5.0	17.5
CKS-16-H		35.7			9.5		
CKS-20-L	23.3	37.0	38.5	18.0	7.7	5.0	20.0
CKS-20-H		40.3			9.5		

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Grey
Std. Package:	100 pcs.




RoHS compliant

Cable Clamp



GXV




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	250 / 500 / 1000pcs.



Part No.	A mm	B mm	C mm	D mm	E mm	Package
GXV-1	13.0	10.0	6.8	2.0	4.0	1000
GXV-2	15.0	13.0	9.0		6.0	
GXV-3	21.6	19.0	12.8	2.2	9.0	500
GXV-4	25.0	20.0	13.2		11.0	250
GXV-5	32.0	25.4	16.0	2.1	13.4	
GXV-6	35.8	24.8	16.8	2.7	18.0	

Cable Clamp

RoHS compliant



XD-4




3M DOUBLE ADHESIVE TAPE
(THICKNESS 1.1mm)

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.


Part No.	Package
XD-4	1000

Cable Clamp




Part No.	Package
XD-6	1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.




XD-6

Cable Clamp



Part No.	Package
XDM-11	1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.




XDM-11




RoHS compliant

Cable Clamp




XDM-8 / 9

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.




Part No.	A mm	B mm	C mm	D mm	E mm	F mm
XDM-8	25.4	6.5	15.5	11.6	7.8	11.3
XDM-9	25.2	12.7	25.2		7.6	11.0

Cable Clamp



XDM-10

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.




Part No.	Package
XDM-10	500




RoHS compliant

Mini Flat Cable Clip




Part No.	Package
FCA-16	100




FCA-16

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Mini Flat Cable Clip




Part No.	Package
FCA-10	100




FCA-10

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Mini Flat Cable Clip



Part No.	Adhesive backing
MFC-2000	No
MFC-3000	Yes





MFC

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Cable Clamp



XDN




3M DOUBLE ADHESIVE TAPE
(THICKNESS 1.1mm)


Material:	Steel
Flame class:	not relevant
Color:	Metal
Std. Package:	500 / 1000 pcs.

Part No.	A mm	B mm	C mm	Package
XDN-1	20.0	10.0	11.6	1000
XDN-2	25.0	15.0	17.1	500

Cord Keep




K




Material:	Steel base, Zinc plated
Color:	Gray
Std. Package:	250 pcs.

Part No.	Adhesive tape
K-103G	10 x 18 mm
K-104G	9.2 x 23.8 mm
K-105G	12.9 x 23.8 mm
K-106G	14.7 x 23.8 mm

Side-Slot Mini Clamp





TMC-6



Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
TMC-6	1000

Cable Clamp





NXT

Part No.	A mm	B mm	C mm	D mm	E mm
NXT-2	13.0	8.5	9.2	6.3	3.0
NXT-3	16.0	11.5	13.0	9.0	2.9

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Cable Clamp





XU

Part No.	A mm	B mm	C mm	D mm	E mm	F mm
XU-1	21.0	15.5	11.5	10.0	17.2	1.1
XU-3	27.0	22.0	18.0	11.2	16.7	0.8

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.

Cable Clamp




XU-2

Part No.	Package
XU-2	1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.


Cable Clamp




XMML-1

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
XMML-1	1000




Cable Clamp




XMML-2

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
XMML-2	1000




Cable Clamp




XMML-3

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
XMML-3	1000





CHASSIS ØE THICKNESS 1.0~1.6


Part No.	A mm	B mm	C mm	D mm	E mm	Package
NXT-6	12.0	8.8	11.5	8.5	3.5	1000
NXT-7	9.2	6.8	7.6	5.0	3.0	2000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 / 2000 pcs.

Cable Clamp



NXT 6/7



CHASSIS Ø3 THICKNESS 1.6


Part No.	Package
NXT-10	1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Cable Clamp



NXT-10



CHASSIS Ø3.5

Part No.	A mm	B mm	Chassis Thickness
NXT-11	3.2	5.20	1.6 mm
NXT-11S	2.8	4.15	1.0 mm

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Cable Clamp




NXT-11




RoHS compliant

Cable Clamp




NXT-12




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
NXT-12	1000

Cable Clamp



NXT-15




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
NXT-15	1000

Mini Wire Saddle - Teardrop Head




NXT-T



Material:	Nylon 66 (UL)
Flame class:	94 V-0
Color:	Natural
Std. Package:	1000 pcs.

Part No.	A mm	B mm	Panel Thick.
NXT-T-1	5.8	1.7	1.6
NXT-T-2	11.2	1.7	
NXT-T-3	11.2	2.3	2.2
NXT-T2-1	5.8	2.45	2.36

Micro Wire Saddle - Arrowhead




NXT-A1/A11

Part No.	A mm	B mm	C mm	D mm	Panel Thick.
NXT-A1-1	7.3	6.7	9.1	1.8	1.6
NXT-A1-2	9.1	8.2	10.8		
NXT-A1-3	11.2	9.4	12.0		
NXT-A1-4	13.0				
NXT-A11-1	7.3	6.7	9.1	2.6	2.4
NXT-A11-2	9.1	8.2	10.8		
NXT-A11-3	11.2	9.4	12.0		
NXT-A11-4	13.0				

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Natural
 Std. Package: 1.000 pcs.

Micro Wire Saddle - Arrowhead



NXT-A2/A21


Part No.	A mm	B mm	C mm	D mm	Panel Thick.
NXT-A2-1	7.3	6.7	9.1	1.8	1.6
NXT-A2-2	9.1	8.2	10.8		
NXT-A2-3	11.2	9.4	12.0		
NXT-A2-4	13.0				
NXT-A21-1	7.3	6.7	9.1	2.6	2.4
NXT-A21-2	9.1	8.2	10.8		
NXT-A21-3	11.2	9.4	12.0		
NXT-A21-4	13.0				

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Natural
 Std. Package: 1.000 pcs.




RoHS compliant

Mini Flat Cable Clip




MFS-1000

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




● Hole Dimensions




Part No.	Package
MFS-1000	100

Side-Slot Mini Clamp




YMC / YMW

Material:	Nylon 6 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.



YMC



YMW


Part No.	A mm	B mm	C mm	Panel thick.	Hole Ø
YMC-05-H-0	10.7	3	11.8	0.5-2.0	Ø3.5
YMC-05-0	10.2		12.7	0.5-1.6	
YMC-10-0	12.0		15.14		
YMC-15-0	13.8		20.5		
YMW-16	12.2	3.5	17.9	0.8-1.8	Ø4

Side-Slot Mini Clamp




LS

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.





■ Type-LS



■ Type-S

Part No.	A mm	B mm	C mm
LS-5	6.8	9.7	17.1
LS-10	10.2	13.7	21.1
S-5	6.6	10.8	17.5
S-10	10.0	13.4	20.9

Super Mini Clamp




MN

Part No.	A mm	Installation	Package
MN-1	5.7	Adhesive tape	500
MB-1		M2.5 Screw	
MN-2	8.5	Adhesive tape	1000
MB-2		M2.5 Screw	
MN-3	10.5	Adhesive tape	1000
MB-3		M2.5 Screw	
MNC-4	-	M2.5 Screw	

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 / 1000 pcs.

Super Mini Clamp



MU


Part No.	A mm
MU-01-1	4
MU-01-2	6
MU-01-3	8
MU-01-4	10
MU-01-5	12
MU-01-6	14
MU-01-7	16
MU-01-8	18

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.




RoHS compliant

Cable Clamp



DIB




CHASSIS $\varnothing 4.8 \sim 5.0$ THICKNESS 0.8~2.0


Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 / 1000 pcs.

Part No.	A mm	B mm	Package
DIB-1	12.0	5.0	1000
DIB-2	17.0	10.0	500
DIB-3	26.0	19.0	
DIB-4	34.0	27.0	

Cable Clamp



WSS-2



CHASSIS $\varnothing 4.8$
THICKNESS 0.8~2.0


Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	Package
WSS-2	1000

Blind Head Mini Wire Saddle



CINXT





Bottom Hole: 7.9mm
Panel Thickness: 6.4mm

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Part No.	A ± 0.4 mm
CINXT-1-66	13.0
CINXT-2-66	18.3
CINXT-3-66	27.2
CINXT-4-66	35.6

Arrow Head Wire Saddle





BXT

Part No.	Part No.	H mm	A mm	B mm
BXT-02	BXT-02V0	16,3	19,6	12,7
BXT-03	BXT-03V0	25,1	28,4	21,6

Material:	Nylon 66 UL
Flame class:	94 V-2 or V0
Color:	Natural
Std. Package:	1.000 pcs.

Wire Saddle



OXT

Part No.	Part No.	H mm	A mm	B mm
OXT-01	OXT-01V0	9,2	12,7	2,8
OXT-02	OXT-02V0	14,4	17,9	8,6
OXT-03	OXT-03V0	23,4	26,9	18,2
OXT-04	OXT-04V0	31,3	34,8	26,1

Material:	Nylon 66 UL
Flame class:	94 V-2 or V0
Color:	Natural
Std. Package:	1.000 pcs.




RoHS compliant

Narrow Wire Saddle - Arrowhead



OXT-A1/A2




Material:	Nylon 66 UL
Flame class:	94 V-2 or V0
Color:	Natural
Std. Package:	1.000 pcs.

Part No.	A mm	B mm	Panel Thick.
OXT-A1-1	13.0	8.2	1.6
OXT-A1-2	18.0		
OXT-A1-3	26.9		
OXT-A1-4	34.8		
OXT-A2-1	13.0	9.8	3.2
OXT-A2-2	18.0		
OXT-A2-3	26.9		
OXT-A2-4	34.8		

Narrow Wire Saddle



OXT





Material:	Nylon 66 UL
Flame class:	94 V-2 or V0
Color:	Natural
Std. Package:	1.000 pcs.

Part No.	A mm
OXT-1	13.0
OXT-2	18.0
OXT-3	26,9
OXT-4	34,8



RoHS compliant

Wire Saddle





WS

Part No.	H mm	A mm	B mm	C mm	W mm
WS-1NS	9.5	13.0	5.0	8.2	11.1
WS-2NS	14.7	18.2	10.2		
WS-3NS	23.7	27.2	19.2		
WS-4NS	31.6	35.1	27.1		
WS-2WS	15.5	19.0	11.2	9.9	16.0
WS-2NS-L	14.7	18.2	10.2		11.1

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Locking Wire Saddle



LWS


Part No.	H mm	A mm	B mm	C mm	D mm	E mm
LWS-1M	13.5	8.0	11.0	19	16	4,8
LWS-2M	19.5	14.0			19	5.2
LWS-3M	28.0	22.3			19	5.2

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




RoHS compliant

Locking Wire Saddle



LWS




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Part No.	H mm	A mm	B mm	C mm	D mm	W mm
LWS-1NS	9.2	12.7	2.8	8.2	2.2	11.0
LWS-2NS	14.4	17.9	8.6			
LWS-3NS	23.4	26.9	18.2			
LWS-4NS	31.3	34.8	26.2			

Locking Wire Saddle



LWS




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Part No.	H mm	A mm	B mm	C mm	D mm	W mm
LWS-1.5S	14.0	18.0	12.5	7.7	2.0	10.4
LWS-2.5S	19.0	23.2	16.5			12.0


RoHS compliant

Locking Wire Saddle




Part No.	A mm
MXT2-1	13.0
MXT2-2	18.0
MXT2-3	27.2
MXT2-4	35.1

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1.000 pcs.



MXT2

Locking Wire Saddle



Part No.	A mm	B mm	Panel Thick.
MXT-A1-1	13.0	8.27	1.6
MXT-A1-2	18.0		
MXT-A1-3	27.2		
MXT-A1-4	35.1		
MXT-A2-1	13.0	9.87	3.2
MXT-A2-2	18.0		
MXT-A2-3	27.2		
MXT-A2-4	35.1		

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1.000 pcs.




MXT-A1/A2




RoHS compliant

Cable Routing



DID



CHASSIS $\varnothing 4.8 \sim \varnothing 5.0$ THICKNESS 1.2~2.4



Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.

Part No.	A mm	B mm
DID-1	16.0	14.0
DID-2	11.1	10.2
DID-3		5.0



RoHS compliant

Locking Wire Saddle





LWS-2Y

Part No.	Package
LWS-2Y	100

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Locking Wire Saddle



LWS

Part No.	H mm	A mm	D mm	W mm	Panel thickness
LWS-1S	7.2	11.2	2.0	11.0	0.8 - 2.3
LWS-3S	10.2	14.2		16.5	
LWS-3S-2W					
LWS-5S-2W	15.2	19.2			
LWS-8S-2.5W	22.7	27.2		18.0	

Part No.	H mm	A mm	D mm	W mm	Panel thickness
LWS-1SL	7.2	11.2	2.0	11.0	1.6 - 3.2
LWS-1.5SL	14.5	18.5		16.5	
LWS-5SL-2W	17.2	21.2		18.0	
LWS-8SL-2.5W	24.7	29.2			

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




RoHS compliant

Locking Wire Saddle




LWS

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




Part No.	ØA mm	B mm
LWS-2W	3.5	8.5
LWS-2W-4	4.2	
LWS-2C	3.5	7.5

Locking Wire Saddle




LWS-2H

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.




Part No.	Package
LWS-2H	100

Locking Wire Saddle




LWS-3H

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.



Part No.	Package
LWS-3H	100

Cable Clamp

CHASSIS $\varnothing 6.0$ THICKNESS 2.0


Part No.	Package
PDD-5	1000



PDD-5

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	1000 pcs.

Cable Clamp

CHASSIS $\varnothing 6.0$ THICKNESS 2.0


Part No.	A mm	B mm
PDD-6	6.2	9.2
PDD-8	8.2	11.2
PDD-10	10.2	13.2



PDD

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.

Cable Clamp

CHASSIS $\varnothing 6.0 \sim \varnothing 6.5$ THICKNESS 0.8~2.5

Part No.	Package
PDDC-15	500




PDDC-15

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Black
Std. Package:	500 pcs.




RoHS compliant

Cable Clamp



DD




ONLY FOR DD-10


Part No.	A mm	B mm	C mm	D mm	Package
DD-1SS	6.5	3.8	3.0	6.8	1000
DD-1S	9.2	5.4		8.2	
DD-1	13.2			8.9	
DD-2	9.7		4.5	10.2	
DD-3	9.5	4.8	6.2	10.2	
DD-4			7.6	10.5	
DD-5			9.0	12.4	
DD-5L	12.3	5.4	11.5	13.2	500
DD-6	12.7	4.8		14.7	
DD-7	12.9	5.4	12.8	16.0	
DD-7S		4.8	15.5	16.7	
DD-8		5.4	17.0	20.2	100
DD-9			20.0	21.2	
DD-10			24-27	23.5	
DD-12	9.9	4.4	3.0	8.5	1000
DD-13	9.5	3.2	8.3	12.0	
DD-14	6.3	3.7	3.5	6.4	
DD-15	9.6	4.4	5.6	12.1	1000
DD-16	11.6	6.4			

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	see table

Cable Clamp




DE



Part No.	Package
DE-16	500

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.





Part No.	Package
DE-12.7	500



RoHS compliant


Nylon Clamp



NK

Part No.	Typ	Inner diameter mm			Diameter mm									Package				
		Outer hole	Center hole	Inner hole	A	B	C	D	E	F	G	H	N					
NK-2N	A	3.0	-	-	3.3	4.3	9.5	-	-	4.8	4.8	1.1	9.5	100				
NK-3N		4.6			5.3	4.3	10.3											
NK-4N		5.6			6.8	4.3	11.1											
NK-5N		7.4			8.4	4.3	11.9											
NK-6N		10.0			10.6	4.3	12.7											
NK-7N		10.7			12.2	4.3	13.5											
NK-8N		11.9			13.2	4.3	14.3			6.3	6.3	1.8	12.7					
NK-9N		13.5			15.2	4.3	15.1											
NK-10N		14.0			16.0	4.3	15.9											
NK-11N		16.8			19.0	5.1	17.5			6.3	7.9							
NK-12N		17.8			19.8	5.1	18.2											
NK-13N		20.8			22.1	5.1	19.0											
NK-14N	B	21.3		18.5	22.9	5.1	19.8	11.9	11.9	6.3	7.9	1.8	12.7	50				
NK-16N		24.4		22.3	26.9	5.1	21.4	13.5										
NK-18N		26.7		24.1	29.2	5.1	23.0	15.1										
NK-24N	C	37.3	35.0	31.2	39.4	5.1	27.8	19.8	11.9	9.5	9.5	1.8	12.7	25				
NK-32N		51.0	46.2	43.7	52.1	5.1	34.1	24.6	13.5									

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Natural



MOUNTING HOLES
 Ø4

Cable Clamp



DMI-6


Part No.	Package
DMI-6	500

Material: Nylon 66 (UL)
 Flame class: 94 V-2
 Color: Natural

Heat Resistant Cable Clamp



KCA




Material:	AFLON
Flame class:	94 V-2
Color:	Blue
Std. Package:	100 pcs.

Part No.	A mm	ØB mm	Bundle diameter
KCA-34	17.45	5.1	Ø4.3
KCA-44	19.00	6.9	Ø5.9
KCA-54	20.95	8.8	Ø7.5
KCA-64	23.75	10.8	Ø9.1

Cable Clamp



DMN-7.5




Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	500 pcs.

Part No.	Package
DMN-7.5	500

RoHS compliant

Snap Clamp




KS

Part No.	A mm	B mm	C mm	Bundle diameter
KS-2S	18.9	8.1	Ø3.8	Ø2.6
KS-5S	26.5	9.4	Ø9.0	Ø7.8
KS-8S	34.7	10.5	Ø15.0	Ø13.0
KS-10S	37.1	11.0	Ø18.0	Ø15.0

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Natural
Std. Package:	100 pcs.

Speed Clamp



NAD


Part No.	Bundle ØA mm	B mm	C mm	D mm	Hole diameter	Panel thickness
NAD-03	Ø5.5	28.0	36.0	4.0	Ø4.8	0.8 - 2.3
NAD-04	Ø6.5	33.0	41.6	6.0		0.8 - 3.2
NAD-06	Ø9.5	43.0	51.6			0.6 - 3.0
NAD-09	Ø14.0	62 0	70.6			
NAD-13	Ø22.0	88.0	99.6			

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Black
Std. Package:	500 pcs.




RoHS compliant

Shell Duct




D




Part No.	Length mm	Dimensions			Bundle Diameter D	Package
		B mm	C mm	T mm		
D-0125	1000	13.0	7.8	1.0	Ø5	100
D 0250		19.5	11.8	1.2	Ø7	
D-0500		28.4	14.6	1.2	Ø11	50
D-0750		38.2	19.2	1.5	Ø15	

Material: PVC
Flame class: 94 V-2
Color: Gray
Std. Package: 50 / 100 pcs.

Shell Clip



SC





Material: PVC
Flame class: 94 V-2
Color: Gray
Std. Package: 100 pcs.

Part No.	Dimensions mm					Bundle Ø mm	
	A	B	C	D	T	E	F
SC-0507	13	13.0	8.0	11	1.0	Ø5	Ø7
SC-0711	20	19.5	10.8	16	1.2	Ø7	Ø11
SC-1115	25	28.4	14.6	20	1.2	Ø11	Ø15
SC-1519	32	38.2	19.2	25	1.5	Ø15	Ø19



RoHS compliant

Spiral Tube



SPP - SPN - SPF

Material	Part No.	Diameter		Wall T mm Thickness	Pitch P mm	Bundle ØC Diameter	Spool
		Outer ØA mm	Inner ØB mm				
Polyethylene	SPP-04L	4.2	2.6	0.80	6.0	Ø3 - 7	100 m
	SPP-06L	6.0	4.0	1.00	8.0	Ø4 - 12	
	SPP-08L	8.0	6.0		10.0	Ø6 - 18	
	SPP-11L	11.0	8.0	1.50	12.0	Ø8 - 25	50 m
	SPP-12L	12.0	9.0			Ø9 - 28	
	SPP-13L	13.0	10.0			Ø10 - 30	
	SPP-15L	15.0	12.0		15.0	Ø12 - 35	
	SPP-18L	18.0	15.0		20.0	Ø15 - 45	
	SPP-24L	24.0	20.0	2.00	22.0	Ø20 - 60	25 m
	SPP-29L	29.0	25.0		28.0	Ø25 - 75	
Nylon	SPN-04L	3.6	2.6	0.50	6.0	Ø3 - 7	100 m
	SPN-06L	5.5	4.0	0.75	8.0	Ø4 - 12	
	SPN-08L	7.5	6.0		10.0	Ø6 - 18	
	SPN-11L	10.6	9.0	0.80	12.0	Ø9 - 28	50 m
	SPN-15L	13.6	12.0		15.0	Ø12 - 35	
	SPN-18L	16.6	15.0		20.0	Ø15 - 45	25 m
	SPN-24L	21.6	20.0		22.0	Ø20 - 60	
	SPN-29L	27.0	25.0	1.00	28.0	Ø25 - 75	
Tefzel	SPF-04	4.2	2.6	0.80	6.0	Ø3 - 7	100 m
	SPF-06	6.0	4.0	1.00	10.0	Ø4 - 12	
	SPF-12	12.0	9.0	1.50	12.0	Ø9 - 28	50 m

Material:	See Table
Flame class:	SPP/SPN=HB, SPF=V0
Color:	Natural
Std. Package:	See Table




RoHS compliant

Strain Relief Bushing




KY xx-x



Material: Nylon 66 (UL), Flame class: 94 V-2, Color: Black

Part No.	Will fit these cable		Chassis dimension		Chassis thickness	Dimension			Section shape	Pack-age
	UL/CSA Description	Size	A mm	B mm	F mm	C mm	D mm	E mm		
KY 2P-4	SPT-1	φ 3X5.6	9.9	8.7	0.8-1.6	10.8	10.4	4.0	Flat type	1000
KY 3P-4	SPT-1		11.0	9.9		12.1		3.2		
KY 3W-1	SPT-1				1.9-2.5	12.5				
KY 4N-4	SPT-2	φ 3.71X7.6	12.7	11.8	0.8-1.6	13.9	10.5	4.0		
		φ 3.8X7.6	13.1							
KY 4K-4	SPT-2	φ 3.71X7.6	12.7	11.8	1.9-2.5					
		φ 3.8X7.6	13.1							
KY 5N-4	SVT	φ 6.4-7.4	12.7	11.5	0.8-1.6	14.2	10.9	4.2	Round type	500
KY 5P-4	SVT				1.9-2.5					
KY 6N-4	SJT3C#18	φ 7.6	15.9	14.0	0.8-1.6	17.8	14.8	5.6		
KY 6P-4	SJT3C#18				1.9-3.2	17.6				
KY 6N3-4	SJT3C#16	φ 8.2-9.2	15.9	14.0	0.8-1.6	17.8	15.0	5.8		
KY 6P3-4	SJT3C#16				1.9-3.2	17.3	14.8			
KY 7N-2	SJT3C#14	φ 9.2-10.5	19.0	16.5	0.8-1.6	21.5	19.1	7.8		100
		φ 11.0	19.8							
KY 7P-2	SJT3C#14	φ 9.2-10.5	19.0		1.9-3.2	21.7	19.4			
		φ 11.0	19.8							

YK Bushing



YK

Part No.	Applicable wire	Hole dimensions		D mm	E mm	Panel thickness F	Package
		ØA mm	B mm				
YK-1	3.3 x 6.6	14.4	12,0	40.0	30.8	2.0	500
	3.6 x 7.2	14.8					
YK-2	2.8 x 5.6	10.9	9.5	23.0	14.0	2.4	100
YKA-1	0.75 mm ²	14,8	13.3	56.0	30.0	2.2	100
	4.5 x 6.2	14,0	13.4				
	5.4 x 8.0	14.5	13.3				
YKL-1	3.3 x 6.6	12.7	11.1	20.4	10.4	2.0	500
	3.6 x 7.2	13.2					

Material:	Nylon 66 (UL)
Flame class:	94 V-2
Color:	Black
Std. Package:	100 / 500 pcs.



RoHS compliant