


3.5mm Shielded Mono Plug

171-3200-EX



3.5mm Shielded Mono Plug



Dimensions: mm

SPECIFICATIONS

Type:	3.5mm High Reliability Shielded Mono Plug with Strain Relief, Insulated Sleeve and U.S. Tip
Temperature:	70°C
Withstand Voltage:	500VAC for 1 Minute
Insulation Resistance:	100MΩ
Contact Resistance:	50MΩ max.
Cap & Plug:	Nickel Plated Brass
Plug Terminal:	Nickel Plated Brass
Plug Insulator:	Ebonite
Threaded Sleeve:	Nickel Plated Brass
Strain Relief:	PVC
RoHS Compliant by Exemption	

Date Last Revised: 6/3/10

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300891

171-3200-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3200-EX](#)