


LTA-Series




The LTA-Series Mini Tippette Snap-in rocker switches are illuminated, single pole and double-insulated. These AC rated switches are also suitable for low voltage DC applications. A variety of actuators, colors and terminations can be specified with ratings up to 20 amps.





Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon or Polycarbonate
- Bezel Material: Nylon


* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]




			
.069[1.75] DIA .250[6.35]	.156[3.96] DIA .375[9.52] .250[6.35]	.055[1.40] DIA .250[6.35] .187[4.74]	6.000[152.40] .500[12.70]
.250 TAB (Q.C.)	SOLDER LUG	.187 TAB (Q.C.)	INTEGRATED WIRE LEAD (no exposed conductors)


TERMINAL TYPE



PADDLE



SHORT PADDLE

MOUNTING HOLE
Panel Thickness:
.020[.508] min. to
.250[6.35] max.

LTA	20	1	-	T	R	-	B	-	/	125N
SERIES	RATING	TERMINATION	ACTUATOR STYLE	ACTUATOR COLOR	BASE COLOR ¹	LENS COLOR ^{2,3}	LAMP VOLTAGE			
LTA OFF-NONE-ON SINGLE POLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC 11 5A 250VAC 10A 125VAC 5A (TUNGSTEN) 125VAC L 20 10A 250VAC 15A 125VAC 3/4HP 125-250VAC 21 10A 250VAC 15A 125VAC 22 10A 250VAC 15A 125VAC 20A 125-250VAC H 3/4HP 125-250VAC	0 SOLDER LUG 1 .250 TAB (QC) 3 .187 TAB (QC) 5 WIRE LEAD	P PADDLE PS PADDLE - SHORT T LIGHTED ROCKER	ROCKER A AMBER C CLEAR G GREEN ³ R RED PADDLE ¹ B BLACK W WHITE	B BLACK W WHITE	A AMBER C CLEAR G GREEN LU BLUE R RED	6V 6 VOLT/ INCANDESCENT 12V 12 VOLT/ INCANDESCENT 18V 18 VOLT/ INCANDESCENT 24V 24 VOLT/ INCANDESCENT 28V 28 VOLT/ INCANDESCENT 125N 125 VOLT/ NEON 250N 250 VOLT/ NEON			

NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "BEZEL" to the end of the catalog number. (ex.) LTA201-TR-B/12V/BEZEL
Imprinting is available. Please specify when ordering.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

¹ Custom colors are available. Consult factory.

² Neon lamps (125 volt or 250 volt) not recommended with green or blue colored indicators.

³ Specify lens color only if actuator style is P or PS.