



MASTER TL-D Super 80

MASTER TL-D Super 80 58W/865 1SL

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

• General Characteristics

Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Cap-Base Information	Green Plate
Bulb	T8 [26 mm]
Life to 10% failures EM	12000 hr
Life to 10% fail	17000 hr
Preheat EL,3h	
Life to 10% fail	10000 hr
Nonpreh EL,3h	
Life to 50% failures EM	15000 hr
Life to 50% fail	20000 hr
Preheat EL,3h	
Life to 50% fail	12000 hr
Nonpreh EL,3h	
LSF EM 2000h Rated, 3h cycle	99 %
LSF EM 4000h Rated, 3h cycle	99 %
LSF EM 6000h Rated, 3h cycle	99 %
LSF EM 8000h Rated, 3h cycle	99 %
LSF EM 12000h	89 %
Rated,3h cycle	
LSF EM 16000h	33 %
Rated,3h cycle	
LSF EM 20000h	2 %
Rated,3h cycle	

• Light Technical Characteristics

Colour Code	865 [CCT of 6500K]
Colour Rendering Index	85 Ra8
Colour Designation	Cool Daylight

Colour Temperature	6500 K
Luminous Flux EM	5000 Lm
25°C, Rated	
Luminous Flux EM	5000 Lm
25°C, Nominal	
Lum Efficacy Rated EM 25°C	86 Lm/W
LLMF EM 2000h	96 %
Rated	
LLMF EM 4000h	95 %
Rated	
LLMF EM 6000h	94 %
Rated	
LLMF EM 8000h	93 %
Rated	
LLMF EM 12000h	92 %
Rated	
LLMF EM 16000h	91 %
Rated	
LLMF EM 20000h	90 %
Rated	
Design Temperature	25 C
Chromaticity Coordinate X	313 -
Chromaticity Coordinate Y	337 -

• Electrical Characteristics

Lamp Wattage	58 W
Lamp Wattage EM	58 W
25°C, Nominal	
Lamp Wattage EM	58.5 W
25°C, Rated	
Lamp Voltage EM	111 V
25°C	

MASTER TL-D Super 80

Lamp Current EM 0.670 A
25°C
Dimmable yes

• Environmental Characteristics

Energy Efficiency A
Label (EEL)
Mercury (Hg) 2.0 mg
Content
Energy consumption 68 kWh
kWh/1000h



• Product Dimensions

Base Face to Base 1500.0 (max) mm
Face A
Insertion Length B 1504.7 (min), 1507.1 (max) mm
Overall Length C 1514.2 (max) mm
Diameter D 28 (max) mm

• Product Data

Order code 632258 40
Full product code 871150063225840
Full product name MASTER TL-D Super 80 58W/865 1SL
Order product name MASTER TL-D Super 80 58W/865 1SL/25
Pieces per pack 1
Packing configuration 25
Packs per outerbox 25
Bar code on pack - EAN1 8711500632258
Bar code on outerbox - EAN3 8711500632265
Logistic code(s) - 12NC 927922086544
ILCOS code FD-58/65/1B-E-G13
Net weight per piece 159.400 gr

Dimensional drawing





G13

MASTER TL-D Super 80 58W/865 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL-D 58W/865	1500.0	1504.7	1507.1	1514.2	28

Photometric data





© 2013 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2013, July 4
data subject to change