






SPECIFICATION

MATERIALS:
HOUSING & INSERT: PBT
COUPLING: BRASS-NICKEL PLATED
O-RING: VITON

ELECTRICAL:
VOLTAGE: 10-30VDC
CURRENT RATING: 4A PER PORT, 12 AMPS MAX.
PROTECTION CLASS: IP68

NOTES:
THREADED PLUG FITTED TO PORTS 1 & 2 ONLY
PROTECTION CAP FITTED TO ALL M12 PORTS
FIXING HOLES TO SUIT M4 SCREWS

SAP-Nummer	alte Artikel-Nr.	Beschreibung	Farbe
SAP-NUMBER	OLD ENGINEERING-No.	DESCRIPTION	COLOR
1201190016	BKY800P-FBP-05	ULTRA-MPIS-8W-8I/O-5M	gelb/YELLOW
1201190026	BKY800P-FBP-10	ULTRA-MPIS-8W-8I/O-10M	gelb/YELLOW

DESCRIPTION EC NO: WEU2010-0165 DRWN: BBRAUCH CH'KD: ---- APPR: FPACHER 2009/11/27	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		 = 0  = 0		mm	INCH	DRAWN BY BBRAUCH	DATE 2009/10/30	ULTRA-MPIS-8W-8I/O-XM -PUR ----			
			4 PLACES	±----	±----	CHECKED BY APOHL	DATE 2009/10/30				
			3 PLACES	±----	±----	APPROVED BY FPACHER	DATE 2009/11/27				
			2 PLACES	±0.05	±----	MATERIAL NO. see table		 MOLEX INCORPORATED			
			1 PLACE	±0.10	±----				DOCUMENT NO. SD-120119-009	SHEET NO. 1 OF 1	
		ANGULAR ± ---- °									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									