



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WIRE SIZE	DIMENSIONS in.			
		±.03 A	±.01 B DIA.	±.01 C DIA.	±.03 D
BSN22	26-22	.79 (20.1)	.08 (2.0)	.04 (1.0)	.47 (1.2)

NOTES:

- USED FOR:
A. #26-22 AWG SOLID OR STRANDED COPPER WIRE
B. 221°F [105°C] MAX. TEMP. RATING
- INSTALLATION TOOLS: CT-520, CT-1525, CT-2500
- WIRE STRIP LENGTH: 1/4 ^{+1/32}₀ [6,4 ^{+0,8}₀]
- MATERIAL:
A. STAMPING: .02" [0,5] THK COPPER, TIN PLATED
B. HOUSING: NYLON, YELLOW
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.



							TITLE BARREL NYLON INSULATED BUTT SPLICE #26-22 CUSTOMER DRAWING					
							ITEM REVISION NAME N41337BA/07			PANDUIT		
							DATASET FILE NAME N41337BA_DC/07A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
							THIRD ANGLE PROJECTION 			MATERIAL: SEE NOTES		
							DRAWING NUMBER: A41337					
07	04-25-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A41337						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DAW	DATE -	CHK -	SCALE NONE	SHT 1 OF 1	SIZE A