


Non-NEMA Twist-Lock® Devices

30 Ampere, 250, 125/250 Volts and 3Ø Y 120/208 Volts AC

Insulgrip® Plugs, Flanged Inlets, Connector Bodies and Receptacles

For Replacement Use Only

IP20
SUITABILITY

Insulgrip Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.360"-.930" (9-24)	HBL3333GC	HBL3333C

Accessories on page B-51.

Single Flush Receptacles

Description	Catalog Numbers	
Black urea face, back wired.	HBL3330G	HBL3330


Accessories on page B-50.

Insulgrip Flanged Receptacles

Description	Catalog Numbers	
Nylon casing, back wired.	—	HBL3335C

Accessories on page B-50.

For Replacement Use Only

IP20
SUITABILITY

Insulgrip Connector Bodies




Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.35"-1.15" (9-29)	HBL3433GCB	HBL3433C

Accessories on page B-53.

Single Flush Receptacles

Description	Catalog Numbers	
Black phenolic, back and side wired.	HBL3430G	HBL3430

Accessories on page B-52.

**HBL3333GC****HBL3330G****HBL3335C****HBL3433GCB****HBL3430**

Note: The devices shown on this page are not listed by Underwriters Laboratories Inc. and are for replacement use only in existing installations.

CAUTION: To avoid electrical shock, review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device.