

SCALE: 1" = 1.5"

UNLESS OTHERWISE  
SPECIFIED  
DIMENSIONS ARE IN MM  
TOLERANCES:  
.XX-- ± 1  
.XXX-- ± .5  
ANGLE-- ± 3°

1).Contact Rating:  
NO: 30 A, 277 V AC, Resistive  
16 FLA, 277 V AC  
1 HP, 120 VAC  
2 HP, 277 VAC

2).Coil Rated Voltage:  
12VDC

Pick-Up: During 75%~110% coil rated voltage should pick up reliably  
Drop-Out: During 10%~70% coil rated voltage should drop out reliably


3).Coil Resistance:  
73 Ω ± 10%

4).Insulation class:  
Class F Insulation

5).Service Life:  
Mechanical Life 1,000,000 Operations  
Electrical Life 100,000 Operations

6).Mark Approved :  
UL : E251539

### Contact Configuration



REV	Description	By	ECO #	Date

**Goodspec** **HongLi**  
Electric

DRAWN BY:	DATE:	TITLE:
Zhao Ping	11/09/2009	RELAY, DPST, 12VDC
CHECKED BY:	DATE:	
Wang qiang	11/21/2014	
APPVD ENG:	DATE:	DRAWING NO:
Xinhua Zhou	11/21/2014	HLR-72ABTAA
APPVD OPS:	DATE:	SHEET
		REV.