

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1952231


DC

HIGH BACK PRESSURE E1225 series



Size: (120 x 120 x 25 mm)
4.72 x 4.72 x 0.98 inches

- Features:** *high back pressure design*
- Construction:** UL94V-0 PBT impeller & frame
- Bearing option:** ball bearing or sleeve
- Connection:** terminal option or AWG 24, UL1007 lead wires
- Frame:** flanged
- Protection:** thermal
- Options:** tachometer output signal;
locked rotor alarm signal



Model No.	Rated Voltage V	Current mA					Revolution		Air Volume		Max Static Pressure (H ₂ O)		Sound Noise	Weight
		5	12	24	48		RPM		M ³ /Min	CFM	MM	INCH	dBA	g
E1225S	5/12/24	220	100	85	-		1,400		1.24	44	2.25	0.09	28	6.28
E1225L	5/12/24	340	142	95	-		1,800		1.55	55	3.00	0.12	32	6.28
E1225M	5/12/24/48	600	245	160	80		2,200		1.89	67	4.50	0.18	36	6.28
E1225H	12/24/48	-	385	240	120		2,600		2.32	82	6.00	0.24	40	6.28
E1225E	12/24/48	-	580	340	170		3,000		2.63	93	7.00	0.28	44	6.28