






LOC		DIST		P	F	REVISIONS					
CM		53				ZONE	LTR	DESCRIPTION		DATE	APPD
						B	REV PER EC 0730-0051-94		4-28-94	RV	
										RS.	



SECTION A-A
SCALE 10:1




SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

1.57	.062	2.79	.110	-	-
1.50	.059	2.41	.095	-	-
1.27	.050	2.29	.090	-	-
0.76	.030	2.16	.085	16.89	.665
0.20	.008	2.08	.082	3.68	.145
0.13	.005	1.91	.075	3.30	.130
MM	IN	MM	IN	MM	IN

CONVERSION TABLE



PRE-TIN	0.20 BRASS	1.27 - 2.79	0.2 - 0.9 mm ² (24-18 AWG)	770983-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± 0.13 ANGLES ± -		DR 7-13-92 K. SALMON CHK 7-13-92 R. SWING APPD 7-16-92 C. CASH MATERIAL APPD 7-16-92 C. CASH PRODUCT SPEC -	AMP AMP Incorporated Harrisburg, PA 17105-3608	
SEE TABLE		APPLICATION SPEC -	SIZE D 00779	DRAWING NO 770983
SEE TABLE		WEIGHT -	SCALE 8:1	SHEET 1 OF 1

.062 PIN,
COMMERCIAL PIN AND SOCKET

CUSTOMER DRAWING