



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Durable PFA Type K & T Exposed Welded Tip Thermocouples



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- ◆ Thermocouple types K & T to ANSI MC96.1
- ◆ Fast response, welded exposed junction
- ◆ 5 metre long Teflon® PFA insulated twin-twisted lead
- ◆ Durable construction with choice of conductor size, 1/0.2, 1/0.3mm solid or 7/0.2mm stranded
- ◆ Miniature plug termination
- ◆ Temperature range -75°C to +250°C
- ◆ Ideal for test & development applications

Thermocouple Type	Conductors Size	Length	Manufactures Part No.	Farnell Order Code
Type K	1/0.2mm	1m	Z2-K-1.0-1/0.2-MP-ANSI	244-3720
Type K	1/0.2mm	2m	Z2-K-2.0-1/0.2-MP-ANSI	244-3721
Type K	1/0.3mm	1m	Z2-K-1.0-1/0.3-MP-ANSI	244-3718
Type K	1/0.3mm	2m	Z2-K-2.0-1/0.3-MP-ANSI	244-3719
Type T	1/0.3mm	1m	Z2-T-1.0-1/0.3-MP-ANSI	244-3726
Type T	1/0.3mm	2m	Z2-T-2.0-1/0.3-MP-ANSI	244-3727
Type K	7/0.2mm	1m	Z2-K-1.0-7/0.2-MP-ANSI	244-3722
Type K	7/0.2mm	2m	Z2-K-2.0-7/0.2-MP-ANSI	244-3723

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com