



- Clamp ties are used to attach a bundle to another surface such as a control panel wall or ceiling using another fastener.
- The design allows for bundling before or after screwing clamp in place.

Part Number: PLC1.5I-S8-C0

Product Family: *Pan-Ty*® Clamp Ties - Weather Resistant

Product Line: Clamp Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Clamp Tie, 6.1", Intermediate cross section

Product Type: Cable Ties

Material: Weather Resistant Nylon 6.6

Color: Black

CSA Certified: Yes

UL Listed (File #E56854): No

UL Recognized (File #E56854): Yes

Length (In.): 6.1

Length (mm): 155

Width (In.):	.135
Width (mm):	3.4
Boss Height (In.):	.166
Boss Height (mm):	4.2
Boss Width (In.):	.335
Boss Width (mm):	8.5
CE Compliant:	Yes
Cross Section:	Intermediate
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.25
Max. Bundle Diameter (mm):	32
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M4
Min. Loop Tensile Strength (Lbs.):	40
Min. Loop Tensile Strength (N):	178
Nominal Hole Diameter (In.):	.174
Nominal Hole Diameter (mm):	4.4
Screw Size:	#8

Std. Pkg. UOM:	PK
Thickness (In.):	.045
Thickness (mm):	1.1
Tool:	GTS, GTSL, GS2B, PTS, PPTS, STS2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100