

# Compact Keyboard

## G81-1800



*Actual product may vary from the image shown*

### Small dimensions and top performance!

This popular 16 inch compact designed PC keyboard is highly sought after for space-saving applications and optimum longevity requirements.

### Facts & Features

- FTSC technology (mechanical individual keys with membrane contact switches)
- High-performance and compact 16" PC keyboard
- Space-saving and ergonomic
- Robust and reliable
- High-quality keyboard for professional users
- Also available without "Windows® keys" (101/102 keys)
- Codeset 3 support e.g. for Unix systems (PS/2 version)
- Also available with or without Windows™ keys

### Technical Data:

#### Total weight (with packaging)

approx. 1.3 kg (without packaging)

approx. 1.6 kg (with packaging)

#### Storage Temperature:

-20 °C to 60 °C

#### Operating temperature:

0 °C to 50 °C

### Compatibility

- Designed for MS Windows™ XP
- Windows™ 2000, XPembedded, Vista, Windows 7
- Works with Linux, Mac, UNIX, Sun

### Current Consumption:

Typ.16 mA

### Interface:

PS/2 or USB

### Number of buttons:

104 = US layout with Windows™ keys

101 = US layout without Windows™ keys

### Agency Approvals / Instructions

- FCC, CE, C-Tick, VDE, cURus

### Delivery Volume:

- G81-1800
- Quick Guide
- CDROM (USB version only)

### System Requirements

- PS/2: Plugs for Keyboard & Mouse
- USB: USB plug & supporting operating system

### Dimensions (product):

approx. 405 x 180 x 44 mm (keyboard)

### Dimensions (packaging):

approx. 460 x 270 x 50 mm (packaging)

### Reliability:

- MTBF > 80.000 hours
- MCBF > 10 bill. operation

### Keyboard:

- Key technology FTSC
- Service life, standard key: >50 million key operations
- Operation characteristics: Linear
- Inscription technology: Laser
- Inscription layout: US
- Number of keys: (see table)

## Technical Data (continued):

### Cable length:

approx. 1.75 m

### Packaging unit:

- Number of products in the master packaging 52 keyboards
- Number of master packages per pallet 2

### Available Software:

- Cherry Keyman (USB version only)
- MS Windows™, 2000, XP, Vista, Windows 7

### Guarantee period:

- 2 years

Errors, technical changes and delivery possibilities accepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

## Order Description

| <i>Order Number</i> | <i>Interface</i> | <i>Number of Keys</i> | <i>Color</i> |
|---------------------|------------------|-----------------------|--------------|
| G81-1800LPAUS-0     | PS/2             | 101                   | Light grey   |
| G81-1800LPAUS-2     | PS/2             | 101                   | Black        |
| G81-1800LPMUS-0     | PS/2             | 104                   | Light grey   |
| G81-1800LPMUS-2     | PS/2             | 104                   | Black        |
| G81-1800LUMUS-0     | USB              | 104                   | Light grey   |
| G81-1800LUMUS-2     | USB              | 104                   | Black        |

(possible country/layout versions, others available on request)

ZF Electronic Systems Pleasant Prairie, LLC  
 11200 88th Avenue  
 Pleasant Prairie, WI 53158  
 USA  
 Phone: 262.942.6500  
 Internet: [www.cherrycorp.com](http://www.cherrycorp.com)

Sales: 262.942.6500  
 E-Mail: [cep\\_sales@zf.com](mailto:cep_sales@zf.com)  
 Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2013 ZF Electronic Systems Pleasant Prairie, LLC  
 Last update: February 5, 2013