


USB-A-D-S-B-TH



USB-A-S-F-O-TH



USB-AM-S-F-W-TH



USB-A-S-F-B-VU



USB-A, USBR-A, USB-AM SERIES

STANDARD & RUGGED USB 2.0

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?USB-A, www.samtec.com?USBR-A or www.samtec.com?USB-AM

Insulator Material:

High Temperature Thermoplastic

Contact Material:

Phosphor Bronze

Plating:

Gold on Contacts,

Nickel on Shell, Tin on Tails

Operating Temp Range:

-50°C to +85°C

Voltage Rating:

30 VAC

Contact Resistance:

30 mΩ

Cycles:

1500 (max tested)

Packaging:

Packaged and shipped in Bulk Packaging Trays; Trays suitable for automation available

RoHS Compliant:

Yes

Lead-Free Solderable

-TH & -VU=Yes

(Wave Solder only)

TID Numbers (USB-A):

USB-A-D-X-X-TH (61001199)

USB-A-S-X-X-TH (61001180)

USB-A-S-X-X-SM2 (61001152)

TID Number (USB-AM):

USB-AM-S-X-X-SM (61001154)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE

A

SHELL TYPE

PLATING

COLOR

TERMINATION

USB
= Standard Connector

USBR
= Increased Retention Connector (Complies with Class 1, DIV II minimum withdrawal requirement of 15N.)

-S
= Single

-D
= Double (-TH option only)

-F
= Gold Flash on Mating Area, Tin on Tails

-S
= 30μ" (0.76 μm) Gold on Mating Area, Tin on Tails

-B
= Black (USB only)





-W
= White (USB only)

-O
= Orange (USBR only)

-TH
= Through-hole

-SM2
= Surface Mount (USB only)

-VU
= Upright, Through-Hole



-D (Requires -TH)

USB

TYPE

SHELL TYPE

PLATING

COLOR

TERMINATION

-AM
= A Type (Plug)

-S
= Single

-F
= Gold Flash on Mating Area, Tin on Tails

-S
= 30μ" (0.76 μm) Gold on Mating Area, Tin on Tails

-B
= Black

-W
= White

-TH
= Through-hole

-SM1
= Surface Mount

