







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
AD	00		B2	REVISED PER ECO-11-004587	11MAR11	RK	HMR



- FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.
- SWITCH SHOWN IN OPEN POSITION.
- ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.
- STAMPING WILL VARY ON 2 AND 3 POSITION TOPS DUE TO SPACE RESTRICTIONS.
- STRIPPABLE TRANSPARENT SEAL, SEE FIG 6.
- .315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300^{+.010}_{-.000} AT MOUNTING SURFACE.
- NO POSITION MARKING.
- NO PART NO. MARKING.
- STRIPPABLE TAPE SEAL, SEE FIGURE 8.
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)
- MATERIAL: HOUSING AND ROCKERS - POLYESTER
CONTACT & SOLDER LEAD - COPPER ALLOY
- FINISH: CONTACT - GOLD OVER NICKEL
SOLDER LEAD - TIN OVER NICKEL
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	FIG 2	FIG 3A& 7		1.08	10	6-5435802-3
	FIG 1	FIG 3B		.88	8	3-5435802-8
	FIG 2			.88	8	3-5435802-0
	FIG 2			.48	4	2-5435802-9
	FIG 2	FIG 3A		1.28	12	2-5435802-2
	FIG 2			1.18	11	2-5435802-1
	FIG 2			1.08	10	2-5435802-0
	FIG 2			.98	9	1-5435802-9
	FIG 2			.78	7	1-5435802-8
	FIG 2			.68	6	1-5435802-7
OBSOLETE	FIG 2			.58	5	1-5435802-6
	FIG 2			.48	4	1-5435802-5
	FIG 2	FIG 3A		1.28	12	1-5435802-2
	FIG 1			.28	2	1-5435802-0
	FIG 2	FIG 3A		.88	8	5435802-9
	FIG 2			1.08	10	5435802-8
	FIG 2			.98	9	5435802-7
	FIG 2			.78	7	5435802-6
	FIG 2			.68	6	5435802-5
	FIG 2			.58	5	5435802-4
5435802-1 SHOWN	FIG 2			.48	4	5435802-3
	FIG 2			.38	3	5435802-2
	FIG 2	FIG 3A		.88	8	5435802-1
	HOUSING	MARKING	PROT-ECTIVE SEAL	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 19-9-89	 TE Connectivity								
DIMENSIONS: INCHES		CHK R. MILLER 19-9-89									
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. LEITER 19-9-89	NAME SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED —								
	0 PLC ± —	PRODUCT SPEC									
	1 PLC ± —	—									
	2 PLC ± —	APPLICATION SPEC									
MATERIAL	3 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
	4 PLC ± .005	—									
	ANGLES ± —	—									
	FINISH	WEIGHT —					A2	00779	C=5435802	—	
		CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 2					REV B2

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00			SEE SHEET 1		




FIG 3A




FIG 3B





FIG 4



PROTECTIVE SEAL

FIG 6





FIG 7



PROTECTIVE SEAL




FIG 8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TALLEY 19-9-89	 TE Connectivity				
		CHK R. MILLER 19-9-89					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. LEITER 19-9-89	NAME				
	0 PLC ± -	PRODUCT SPEC	SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, SIDE ACTUATED -				
	1 PLC ± -	—					
	2 PLC ± -	APPLICATION SPEC					
	3 PLC ± .005	—					
4 PLC ± -	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL	FINISH	WEIGHT	A2 00779		C=5435802	—	
SEE SHEET 1	SEE SHEET 1	CUSTOMER DRAWING			SCALE 4:1	SHEET 2 of 2	REV B2