




SERRATIONS

1

4.19 MAX DIA

[.165]

BRAZED SEAM

3.68±0.08

[.145±.003]

FOR #6 STUD

7.54±0.20

[.297±.008]

2.16 MIN DIA

[.085]

9.75 MAX

[.384]

5.16 MIN

[.203]

3.58±0.13

[.141±.005]

0.79±0.05

[.031±.002]

13.46 MAX

[.530]

1

2

3

STAMP AMP 16-14*, APPROX AS SHOWN

COPPER PER ASTM B-152, ANNEALED

0.00254 [.000100] MIN TIN PER ASTM B-545

100

LOOSE PIECE, BOX

8-322996-1

5000

ON TAPE

2-322996-1

--

LOOSE PIECE

322996

QTY

PACKAGE TYPE

PART NUMBER

CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE:

170°C MAX

VOLTAGE RATING:

N/A

CIRCULAR MIL AREA:

1.04-2.62mm² [2,050-5,180]

SOLID OR STRANDED

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

TOOLING INFORMATION

1-800-526-5142

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20 [.008]

3 PLC ± -

4 PLC ± -

ANGLES ± ±

FINISH

2

3

MATERIAL

2

3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

1-28-93

TA BRINKMAN

CHK

1-28-93

DA PATTERSON

APVD

1-28-93

JL MECKLEY

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

TE Connectivity

NAME

TERMINAL, SPADE TONGUE, SOLISTRAND

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

G-322996

1

OF 1

REV

C2

CUSTOMER DRAWING

SCALE

10:1

SHEET

1

OF 1

REV

C2