

DURACELL®

Rechargeable

DC1500

Size: AA 1300 mAh (HR6)
Rechargeable NiMH Battery

NiMH

Technical Specifications



Classification:	Cylindrical Rechargeable
Chemical system	Nickel Metal Hydride (Ni-MH)
Designation:	IEC – HR6
Nominal Voltage:	1.2V
Operating Voltage:	1.0V-1.35V
Operating temp:	-10°C to 50°C
Storage Temp:	5°C – 30°C
Typical weight:	28g
Typical Volume:	8.3 cubic centimeters
Typical Impedance:	20 milliohm @ 1 khz
Rated Capacity:	1300 mAh
Safety Features:	Pressure released resettable vent

BENEFITS


Stays charged for up to 6 months.*

1 charge up to 60 hours in wireless mouse



1 charge up to 13 hours in gaming controller

1 charge up to 270 pictures


Low Rate Discharge



High Rate Discharge



Fast Charge (Charge control required)



DURACELL®
BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Tel: Toll free 1.800.544.5454
Web: www.Duracell.com

*When not in use.

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.

Document #: CH-A