




- 1. MATERIAL: HOUSING—POLYCARBONATE, CLEAR
TERMINAL — .36 [.014] THICK PHOSPHOR BRONZE PLATED
WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED
PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM
NICKEL IN LOCALIZED PLATE AREA OVER
2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
- 2. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS
OTHERWISE SPECIFIED.
- 3. PLUG WILL ACCEPT 0.737[.029] — 0.99[.039] DIAMETER
STRANDED WIRE, 26 OR 28 AWG WITH A 4.57 [.180]
DIAMETER JACKET.
- 4. TERMINATED DIMENSION 6.15 [.242]
MAXIMUM.
- 5. LATCH SHALL BE IN POSITION SHOWN IN DETAIL A
AFTER CRIMPING.
- 7. 500 ASSEMBLIES PER PACKAGE.
- 8. 100 ASSEMBLIES PER PACKAGE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 28MAR2008	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK B. MCNEILL 31MAR2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. MCNEILL 31MAR2008		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		
MATERIAL		NAME MODULAR PLUG ASSEMBLY, 6 POSITION, LONG BODY ROUND CABLE		RESTRICTED TO —
1		SIZE A2		CAGE CODE 00779
1		DRAWING NO 555177		REV K
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1