



General ordering data

Order No.	1777630000
Part designation	SKMU EMV M20
Version	Locknut, Brass, nickel-plated, External thread: M 20 x 1.5
EAN	4032248157907
Qty.	50 pc(s).

General details

AF size 1	24 mm
External thread	M 20 x 1.5
Internal thread	M 20 x 1.5
Length of thread	3.6 mm
Material	Brass, nickel-plated
Thickness	3.6 mm
Type of cable gland	metric

Approvals

Approvals institutes	n.a.
----------------------	------

Classifications

ETIM 2.0	EC000940
ETIM 3.0	EC000940
eClass 4.1	23-11-07-01
eClass 5.0	23-11-07-01
eClass 5.1	23-11-07-01

Similar products

Order No.	Part designation	Version
1777610000	SKMU EMV M12	Locknut, Brass, nickel-plated, External thread: M 12 x 1.5
1777620000	SKMU EMV M16	Locknut, Brass, nickel-plated, External thread: M 16 x 1.5
1777640000	SKMU EMV M25	Locknut, Brass, nickel-plated, External thread: M 25 x 1.5

1777650000	SKMU EMV M32	Locknut, Brass, nickel-plated, External thread: M 32 x 1.5
1777660000	SKMU EMV M40	Locknut, Brass, nickel-plated, External thread: M 40 x 1.5
1777670000	SKMU EMV M50	Locknut, Brass, nickel-plated, External thread: M 50 x 1.5
1777680000	SKMU EMV M63	Locknut, Brass, nickel-plated, External thread: M 63 x 1.5
1718920000	SKMU EMV PG11	Locknut, Brass, nickel-plated, External thread: PG 11
1718930000	SKMU EMV PG13,5	Locknut, Brass, nickel-plated, External thread: PG 13.5
1718940000	SKMU EMV PG16	Locknut, Brass, nickel-plated, External thread: PG 16
1718950000	SKMU EMV PG21	Locknut, Brass, nickel-plated, External thread: PG 21
1718960000	SKMU EMV PG29	Locknut, Brass, nickel-plated, External thread: PG 29
1777700000	SKMU EMV PG 42	Locknut, Brass, nickel-plated, External thread: PG 42
1718900000	SKMU EMV PG7	Locknut, Brass, nickel-plated, External thread: PG 7
1718910000	SKMU EMV PG9	Locknut, Brass, nickel-plated, External thread: PG 9