



DAMM15PX

Part Number Details

Global Mfg Part No.	051520-0029
series	D*M
category	D Sub
line	D Sub
brand	Cannon
ittPartNo	DAMM-15P-X

General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	500
Contact Arrangement	15 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Straight Solder
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 2)
Hardware	.120" (3,05mm) Through Hole
rohsCompliantString	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2011/65/EU
rohsCompliantFlag	NO

Drawings for this part are available. Upon request your will be asked to provide your contact information at which time the appropriate drawing files will be sent to you via email.

[Request 3D Model](#)

A datasheet is available for download.

[Download Datasheet PDF](#)

Check the stock availability of this product at our distributors.

Check Stock Now

Part Number	Distributor	Qty	Location
<a href="#">DAMM15PX</a>	<a href="#">Newark element14</a>	554	United States

<a href="#">DAMM-15P-X</a>	<a href="#">Digi-Key Electronics</a>	554	United States
<a href="#">DAMM15PXA101</a>	<a href="#">TTI Inc</a>	100	United States
<a href="#">DAMM15PXA101</a>	<a href="#">PEI-Genesis, Inc.</a>	1231	United States
<a href="#">DAMM-15P-X</a>	<a href="#">Arrow Electronics</a>	982	United States
<a href="#">DAMM15PX</a>	<a href="#">Digi-Key Electronics</a>	554	United States
<a href="#">DAMM15PX</a>	<a href="#">Farnell element14</a>	3984	United Kingdom

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS. ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the “Contact Us” at the top of every page.

globalManufPartNo: 051520-0029; line: D Sub; ittPartNo: DAMM-15P-X  
[Request a Quote](#)