












プリント基板取付寸法図
DIMENSION FOR P.C. BOARD



DETAIL B
SCALE 20:1



DETAIL D
SCALE 20:1

1. 嵌合相手コネクタ品番: 1376360
- △. 図号: FIG. 1参照
3. 適用ねじ: JIS B1115, B1122タッピンねじ. ねじ径3. 長さはTABLE-2参照
4. ねじ締付けトルク(参考): 0.392N・m MAX. 但し. 管理値は別途規定すること
5. 本製品の取扱は取扱説明書 No. 411-5927に従うこと
- △. [Z]より8mmの位置で測定.
- △. コンタクト仕上確認用マーク

1. MATING CONNECTOR PART NO.: 1376360
- △. CIRCUIT NUMBER: SEE FIG. 1
3. APPLICABLE SCREW: PAN-HEADED, TYPE2 TAPPING SCREW OF NOMINAL DIAMETER 3mm REFER TO JIS B1115, B1122 LENGTH: SEE TABLE-2
4. FASTENING TORQUE (FOR REFERENCE): 0.392N・m MAX BUT TORQUE FOR OPERATION SHOULD BE PROVIDED RESPECTIVELY
5. HANDLING OF THIS PART SHOULD FOLLOW INSTRUCTION SHEET No. 411-5927
- △. MEASURED AT 8mm FROM [Z]
- △. MARKING FOR DESCERMENT OF THE CONTACT FINISH





FIG. 1 CIRCUIT NUMBERS

TABLE-1

SEE DWG 1376357-8										2-1376357-0	
SEE DWG 1376357-8										1-1376357-9	
SEE DWG 1376357-8										1-1376357-8	
SEE DWG 1376357-8										1-1376357-7	
SEE DWG 1376357-8										1-1376357-4	
SEE DWG 1376357-8										1-1376357-3	
SEE DWG 1376357-8										1-1376357-2	
SEE DWG 1376357-8										1-1376357-1	
SEE DWG 1376357-8										1-1376357-0	
SEE DWG 1376357-8										1376357-9	
SEE DWG 1376357-8										1376357-8	
CARTON BOX タンボ-ル箱	PLASTIC TUBE プラスチックチューブ	62	SELECTIVE-TIN (MATTE)	-	1~3 10~12	18~23	-	4~9 13~17,24~26	NATURAL 自然色	6376357-4	
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	62	SELECTIVE-TIN (MATTE)	-	1~3 10~12	18~23	-	4~9 13~17,24~26	NATURAL 自然色	6376357-2	
CARTON BOX タンボ-ル箱	PLASTIC TUBE プラスチックチューブ	7	SELECTIVE-TIN (MATTE)	-	1~3 10~12	4~9 18~23	-	13~17,24~26	NATURAL 自然色	1-1376357-6	
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	7	SELECTIVE-TIN (MATTE)	-	1~3 10~12	4~9 18~23	-	13~17,24~26	NATURAL 自然色	1-1376357-5	
CARTON BOX タンボ-ル箱	PLASTIC TUBE プラスチックチューブ	2	PRE-TIN TIN-LEAD	1~3 10~12	-	18~23	4~9 13~17,24~26	-	NATURAL 自然色	1376357-4	
CARTON BOX タンボ-ル箱	PLASTIC TUBE プラスチックチューブ	1	PRE-TIN	1~3 10~12	-	-	4~9 13~26	-	NATURAL 自然色	1376357-3	
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	1	PRE-TIN	1~3 10~12	-	-	4~9 13~26	-	NATURAL 自然色	1376357-1	
OUTER 外装	INNER 内装	 MARKING マーキング	SOLDERING SIDE 半田付け側	PRE-TIN	SELECTIVE-TIN	SELECTIVE GOLD	PRE-TIN	SELECTIVE-TIN	COLOR 色	PART NUMBER 型番	
PACKING STYLE 梱包形態				 09011 TAB POWER		 025 TAB SIGNAL					
				CONTACT SIDE 接触部側							
				CONTACT FINISH 端子仕上げ							


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. NAGAI 14OCT2000		 TE Connectivity					
DIMENSIONS: mm				CHK T. HAYASHI 14OCT2000							
TOLERANCES UNLESS OTHERWISE SPECIFIED: mm 0.25±0.3				APVD N. SAI 14OCT2000		NAME 025/090 SERIES CONNECTOR 26POSITION CAP HOUSING ASSEMBLY					
				9-PLC 1-PLC 2-PLC 3-PLC 4-PLC TOLERANCES UNLESS OTHERWISE SPECIFIED: mm 0.25±0.3 0.10-0.10 0.05-0.05 0.00±0.01 ANGLES FINISH RZ		PRODUCT SPEC 108-5667 APPLICATION SPEC 114-5250		RESTRICTED TO			
MATERIAL PBT:BRASS				SEE TABLE-1		SIZE A1		CAGE CODE 00779		DRAWING NO C=1376357	
				WEIGHT 9.93 g		SHEET 2 of 2		REV A4			

LOC	DIST	REVISIONS				
J	—//—	P	LTR	DESCRIPTION	DATE	DWN
				SEE 1 OF 2		APVD



CAP ASSEMBLY AND PLUG ASSEMBLY ENGAGEMENT DRAWING

キャップアッセンブリー & プラグアッセンブリー 嵌合図

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. NAGAI 14OCT2000	TE Connectivity					
		CHK T. HAYASHI 14OCT2000						
		APVD N. SAI 14OCT2000						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 = ± 0.3		NAME 025/090 SERIES CONNECTOR 26POSITION CAP HOUSING ASSEMBLY				
		0 PLC ±						
		1 PLC ±0.1						
		2 PLC ±0.01						
		3 PLC ±0.001		PRODUCT SPEC SEE 1 OF 2				
		4 PLC ±0.000J						
		ANGLES ±3'00"						
MATERIAL SEE 1 OF 2		FINISH SEE 1 OF 2		SIZE A3		CAGE CODE 00779	DRAWING NO C-1376357	RESTRICTED TO —//—
CUSTOMER DRAWING				SCALE 2:1		SHEET 2 OF 2		REV A4