

A

B

C




D

A

B

C

D



MATERIAL:

Thermoplastic

TEMPERATURE RANGE:

-Climatic category -55° / +125°

PACKAGING:

Per 100 pieces

COLOUR

Black


NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in 6S-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see 6S-14-920.

Dimensions are in millimeters

Shell size	Number of contacts	A $+0.9$ -0.2	B $+0.10$ 0	C ± 0.05	D ± 0.10	E ± 0.10	F ± 0.10	G ± 0.10	PART NUMBER
E	09	30.60	12.50	24.99	19.00	10.50	9.90	18.20	86305002BLF
A	15	38.90	12.50	33.32	20.60	12.50	9.90	22.80	863026BLF
B	25	52.80	12.50	47.04	23.60	17.00	9.90	29.40	863027BLF
C	37	69.10	12.50	63.50	29.00	24.00	9.90	37.00	863028BLF
D	50	66.70	15.30	61.11	28.00	24.00	12.70	35.00	863029BLF

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	JOUBERT	1999/01/04	ANGULAR	LINEAR	0.X	± 0.1	size A3	Scale 5		
Eng	PESSON	1999/01/04			0.XX	± 0.1				
Chr	LEGARE	1999/01/04			0.XXX	± 0.1				
Appr	LEGARE	1999/01/04	Product family				D-SUB	ECN LS08-0186 Spec ref -		
			title POTTING PLASTIC HOODS right angle exit				dwg no C01-8655-1523		Rev. H	
catalog no			-				CUSTOMER		sheet 1 of 1	

rev	ecn no	dr	date
B	LS05-0026	MPE	2005/07/08
C	LS05-0084	MPE	2005/09/29
D	LS06-0095	LGO	2006/07/24
E	LS07-0249	MPE	2007/10/02
F	LS07-0258	LGO	2007/10/16
G	LS08-0146	MPE	2008/06/16
H	LS08-0186	MPE	2008/09/04



POTTING PLASTIC HOODS
right angle exit

catalog no

title

right angle exit

catalog no

-

customer

sheet 1 of 1

Rev.

H

C01-8655-1523

customer

sheet 1 of 1

Rev.

H

C01-8655-1523

customer

sheet 1 of 1