

2107- ~~XXXXX~~

1=CHAIN

BARREL I.D.

6=24-30 AWG

PART NO.	ENG. NO.	OLD ENG. NO.
02-05-1116	2107-1B6N1	2107-T
02-05-1117	2107-1B6N2	2107-TL
02-05-1104	2107-1B5N1	1129-T
02-05-1105	2107-1B5N2	1129-TL
02-05-3205	2107-2A5N2	2123-L
02-05-1204	2107-2B5N1	2123-T
02-05-1205	2107-2B5N2	2123-TL
02-05-1216	2107-2B6N1	
02-05-1217	2107-2B	

[illegible]

FINISHES:

D= (P562) SELECT GOLD PLATE .000020/(0.00051) MIN. IN CONTACT AREA
OVER .000030/(0.00076) MIN. NICKEL OVERALL.

G= (P550) SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA
OVER .000030/(0.00076) MIN. NICKEL OVERALL WITH
.000010/(0.00025) MAX. GOLD FLASH OVERALL.

5. THESE TERMINALS FOR USE WITH .045/(1,14) ROUND AND SQUARE PINS.
6. THESE TERMINALS WILL ACCEPT STRANDED WIRE WITH .031/(0,79) MAX. THICK INSULATION.
7. A 2° MAX. ANGLE IS ALLOWED.