






REV.	DATE	ECR NO.	DESCRIPTION
NC	05/19/10	XXXXXX	INITIAL RELEASE



RECOMMENDED
MOUNTING HOLE



1. SEALING REQUIREMENT: IP-68 MUST WITHSTAND 3' DEPTH OF WATER FOR ONE HOUR WITHOUT ANY SIGNS OF LEAKAGE
2. MAX. PANEL THICKNESS= 3mm

7	HEX NUT	STAINLESS STEEL	PASSIVATED	1
6	LOCK WASHER	BRASS	GOLD	1
5	GASKET	SILICONE	RED	1
4	CONTACT PIN	BER. COPPER	GOLD	1
3	O-RING	SILICON RUBBER	RED	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	STAINLESS STEEL	PASSIVATED	1
	DESCRIPTION	MATERIAL	FINISH	QTY
			DO NOT SCALE DRAWING	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:

0.5 - 8mm \pm 0.20mm

8 - 30mm \pm 0.40mm

30 - 120mm \pm 0.50mm

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR INCHES ARE:

.020 - .315 = \pm 0.007"

.315 - 1.180 = \pm 0.015"

1.180 - 4.724 = \pm 0.020"

APPROVALS		DATE
DRAWN	M.ZHANG	05/19/10

CHECKED

ISSUED

SHEET 1 OF 1

CAD FILE

C:/CONNEX/132170-12SS.DWG

PART DESCRIPTION	SMA BULKHEAD JACK TO JACK ADAPTOR (IP 68)		
	132170-12SS		
	DWG. NO.	132170-12SS.DWG	REV. NC
	SIZE	A	SCALE NA

Amphenol Connex

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132170-12SS](#)