




5 AND 15MHz SWEEP FUNCTION GENERATORS



- 0.01Hz to 15MHz in 7 steps (Type 72-7650)
- 0.01H to 5MHz in 7 steps (Type 72-7210)
- Built-in Int. Ext. 50MHz frequency counter
- Frequency, symmetry, linear sweep, DC offset and amplitude function
- AM, FM, and EXT. modulation (Type 72-7650 only)
- Output waveform: Sine, Triangle, Square, DC and Sync output
- Output Amplitude: 10 Vp-p Adjustable @ 50.
- Offset level: $\square$ } 10V adjustable @ open circuit
- Includes owners manual and power cord
- CE compliant

SPECIFICATIONS

Model	Type 72-7650	Type 72-7210
Frequency	0.01Hz ~ 15MHz, 7 Ranges	0.01Hz ~ 15MHz, 7 Ranges
Display	5 Digit LED	4 Digit LED
Sweep Time / Rate	10 msec ~ 5 sec. / 1:1 ~ 1:100	10 msec ~ 5 sec. / 1:1 ~ 1:100
Power Requirements	100/120/220/240VAC (Selectable) 50/60Hz	
Dimensions	261 (W) x 71(H) x 211 (D) mm	
Weight	3kg	1.6 kg

Type	Description	Stock No.
72-7210	5MHz Sweep Function Generator	96H8195
72-7210C	5MHz Sweep Function Generator w/Calibration	02J7822
72-7650	15MHz Sweep Function Generator	96H8196
72-7650C	15MHz Sweep Function Generator w/Calibration	02J7823

Distributed by Newark InOne
1-800-4-NEWARK (1-800-463-9275)