








- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR BRONZE.
- △ CONTACT FINISH:
 - UNDERPLATE (ENTIRE CONTACT): 0.00127 MIN NICKEL.
 - ON MATING SURFACES: CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT.
 - ON LEADS: 0.00381 MIN TIN-LEAD OVER UNDERPLATE.
 - LUBRICATION (ENTIRE CONTACT): SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- △ PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED APPROXIMATELY AS SHOWN.
- △ PART TO BE MARKED WITH DATE CODE ONLY.



RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
COMPONENT SIDE

3	6.50
2	5.75
1	5.00
CONTACT NUMBER	DIM Y

ROW	D	2	1	1	3	1	D	ROW
	C	2	1	1	3	1	C	
	B	2	1	1	3	1	B	
	A	2	1	1	3	1	A	
COLUMN	1	2	3	4	5	6	COLUMN	
CONTACT LOADING CHART BY ITEM NUMBER								

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ± -
- 1 PLC ± -
- 2 PLC ± 0.13
- 3 PLC ± -
- 4 PLC ± -
- ANGLES ± -

MATERIAL

FINISH

DWN T. SHUEY 3-12-99

CHK C. SCHMID 3-16-99

APVD C. SCHMID 3-16-99

PRODUCT SPEC 108-1441

APPLICATION SPEC 114-1075

WEIGHT

CUSTOMER DRAWING

NAME PIN ASSY,Z-PACK 2mm FB,RIGHT ANGLE, 4 ROW,24 POSITION,SEQUENCED

SIZE A1

CAGE CODE 00779

DRAWING NO 223532

RESTRICTED TO

SCALE 4:1

SHEET 1 OF 1

REV D2

223532-1

FINISH

PART NUMBER