




## PANEL RECEPTACLES

| Description                                     | Dimensions, in. (mm) |                |   |   | MTG Hole | Construction Notes |      |      | Military Number | Amphenol Number        | Fig |
|-------------------------------------------------|----------------------|----------------|---|---|----------|--------------------|------|------|-----------------|------------------------|-----|
|                                                 | a                    | b              | c | e |          | CAI                | Plt. | Ins. |                 |                        |     |
| Solder Cup Terminal                             | 1.88<br>(47.6)       | 1.19<br>(30.2) | — | — | W        | —                  | P1   | D1   | UG-560          | <a href="#">82-805</a> | 1   |
| Solder Cup Terminal<br>(Copolymer Styrene Ins.) | 1.53<br>(38.9)       | 1.19<br>(30.2) | — | — | U        | —                  | P1   | D6   | UG-496          | <a href="#">82-92</a>  | 1   |

## BULKHEAD RECEPTACLES

| Description               | Dimensions, in. (mm) |                |   |               | MTG Hole | Construction Notes |      |      | Military Number | Amphenol Number        | Fig |
|---------------------------|----------------------|----------------|---|---------------|----------|--------------------|------|------|-----------------|------------------------|-----|
|                           | a                    | b              | c | e             |          | CAI                | Plt. | Ins. |                 |                        |     |
| Rear Mount/Spade Terminal | 1.77<br>(44.8)       | 1.25<br>(31.8) | — | .187<br>(4.7) | Y        | —                  | P1   | D1   | —               | <a href="#">82-843</a> | 2   |

## ANGLE ADAPTERS

| Description                           | Dimensions, in. (mm) |                |                |   | MTG Hole | Construction Notes |      |      | Military Number | Amphenol Number       | Fig |
|---------------------------------------|----------------------|----------------|----------------|---|----------|--------------------|------|------|-----------------|-----------------------|-----|
|                                       | a                    | b              | c              | e |          | CAI                | Plt. | Ins. |                 |                       |     |
| Jack-Plug<br>(Copolymer Styrene Ins.) | 1.53<br>(38.9)       | .875<br>(22.2) | 1.46<br>(37.3) | — | —        | —                  | P1   | D6   | UG-212A         | <a href="#">82-91</a> | 3   |

## BULKHEAD ADAPTERS

| Description | Dimensions, in. (mm) |                |   |               | MTG Hole | Construction Notes |      |      | Military Number | Amphenol Number       | Fig |
|-------------|----------------------|----------------|---|---------------|----------|--------------------|------|------|-----------------|-----------------------|-----|
|             | a                    | b              | c | e             |          | CAI                | Plt. | Ins. |                 |                       |     |
| Jack-Jack   | 1.97<br>(50.0)       | 1.00<br>(25.4) | — | .343<br>(8.7) | Z        | —                  | P1   | D1   | UG-1019         | <a href="#">11050</a> | 4   |

## DIELECTRIC TRIM TOOL

| Description          | Dimensions, in. (mm) |                |                |   | MTG Hole | Construction Notes |      |      | Military Number | Amphenol Number         | Fig |
|----------------------|----------------------|----------------|----------------|---|----------|--------------------|------|------|-----------------|-------------------------|-----|
|                      | a                    | b              | c              | e |          | CAI                | Plt. | Ins. |                 |                         |     |
| Dielectric Trim Tool | 1.47<br>(37.3)       | .625<br>(15.9) | .500<br>(12.7) | — | —        | —                  |      |      | MX-103/U        | <a href="#">103-301</a> | 5   |