

COMMUNICATION DYNAMIC MICROPHONE for CB and Amateur Applications

Everyone can now enjoy a microphone with superior specifications at a moderate price. Features four (4) conductors, (1 shielded), in a 6-ft. coiled cable designed for relay or electronic switching in transmitters, transceivers and PA amplifiers.

Full size, press-to-talk switch extends over half the length of this hand-held mike. High impact shockproof case is attractively styled in matte finish mid-night black. Supplied with rear hang-er button.

Specifications:

Directivity: Omni - Directional

Sensitivity: -72dB $\pm$ 4db at 1KHz

Frequency Response: 200Hz - 5KHz



No. CM43A

S.W.R. Bridge and Field Strength Meter

Perfect dual-purpose meter for checking SWR measurements, as well as reading the field strength in both mobile and home station rigs. Can monitor transmitter outputs in the circuit continuously.



Specifications:

SWR: 1:1 to 1:3

RF Power: 0.5-10W and 0.5-100W Switchable

Accuracy: SWR: +5% Power: +10%

Impedance: 52 ohms

Meter Sensitivity: 200 μ A

Freq. Range: 1.7 to 150 MHz

Size: 5-3/4"H x 2-1/4"D x 1-15/16"

Attractive black metal cabinet supplied with detachable antenna, and set of instructions.

No. FS45

Polarized Automotive Power Cord

No. TC3616

5 ft. Polarized 3-pin connector red lead contains fuse holder and 2 amp fuse 18 Ga. leads.



Automotive Power Cord

No. TC3640

5 ft.; 16 Ga. red and black leads with fuse holder in-line in red lead with 10 amp fuse. Both ends stripped.



In-Line Fuse Holder for Blade Type Fuses

No. FH101

- Material - Bakelite
- Max. Rating: 250VAC/30A
- Color - Black



FUSE HOLDER (Screw Type Cap)



No. 526 - For 3 AG Type Fuse (1/4" x 1-1/4")

No. 525 - For GMA Type Fuse (5mm x 20mm)

Fuse Mounting Bases

No. H108A - Single Fuse

No. H108B - Double Fuse



Will accommodate the 3AG cartridge type auto fuse. Clips are made of spring brass, and mounting board is made of 1/8" XP laminated phenolic insulating material.

MICROPHONE HANG-UP HOLDER with mounting hardware

Stainless Steel



No. H200SS

No. H200SSB bulk packed

Screw Cap Fuse Holder

No. FH55

No. FH55B - bulk packaged

Rating 15A @ 250VAC
Holds 1/4" x 1-1/4" fuses. Can be used in panels up to 1/4" thick. Mounts in 19/32" hole. Overall length of holder 2", behind panel 1-3/8".



In-Line Fuse Holder

No. FH65

No. FH65B - bulk packaged

Holds 1/4" x 1-1/4" fuses. Spring loaded, twist lock design. Plastic housing provides full insulation. 10" heavy duty #18 gauge stranded insulated wire at each end.



REPLACEMENT SCREWS for CB's, PA's, Car Mounts, etc.



No. K40 Size 4 mm

No. K50 Size 5 mm

No. K60 Size 6 mm

For connecting mounting brackets to metal cases. Made of machined brass with a heavy nickel plated finish. Length of threaded portion is 3/8". Packed two per package.

Add suffix "B" to part number for bulk pack.

Heavy Duty In-Line Fuse Holder 10A @ 250V AC

No. 506 - for 3AG type fuse (1/4" x 1-1/4")

No. 507 - for GMA type fuse (5.0mm x 20mm)



SMA TO UHF HT ADAPTOR CABLE

For hand-held Ham or Business Transceivers (HT) with SMA antenna connectors; adapts the antenna connection to a UHF female for connection to mobile or base antennas with a PL-259 termination. The cable is 16" long miniature 50 ohm coaxial cable (RG174/U). Using an adaptor cable will help to reduce strain on the radio's SMA antenna jack.



No. CA740