

Flat zack marker sheet - ZBFM 4/WH,LGS:1-100 - 0800268

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Flat zack marker sheet, Sheet, white, Labeled, Printed horizontally: Consecutive numbers from 1 - 100, Mounting type: Snap into flat marker groove, For terminal block width: 4.2 mm, Lettering field: 4.2 x 5.2 mm

The illustration shows the versions ZBM and ZBFM

Product description

Flat zack marker sheet, Sheet, white, Labeled, Printed horizontally: Consecutive numbers from 1 - 100, Mounting type: Snap into flat marker groove, For terminal block width: 4.2 mm, Lettering field: 4.2 x 5.2 mm

Key commercial data

Packing unit	1
Minimum order quantity	10
GTIN	 4 017918 005863
Weight per piece (including packing)	0.0 GRM
Weight per Piece (excluding packing)	3.47 GRM
Country of origin	GERMANY

Technical data

General

Width (a)	4 mm
Color	white
Inflammability class according to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C
Components	free from silicone and halogen
Pitch	4.2 mm
Material	PA
Printing direction	Printed horizontally
Printing	Consecutive numbers from 1 - 100
Number of individual labels	100
Number of individual labels per row	10
Pitch	4.2 mm

Flat zack marker sheet - ZBFM 4/WH,LGS:1-100 - 0800268

Classifications

eclass

eClass 4.0	24190208
eClass 4.1	24190208
eClass 5.0	27149103
eClass 5.1	27149103
eClass 6.0	27141137

etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410