

Soberton Inc.

Product Data Sheet


Part No. PT-2408 Non-Washable Type

PT-2408

DIMENSIONS



$\phi 24.0 \times H7.5$



Type	Unit	PT-2408
Rated Voltage Square Wave	(Vpp)	5
Operating Voltage	(Vpp)	1~30
Current Consumption	(mA)	< or = 1
Capacitance at 120 Hz	(pF)	15000 $\pm$ 30%
Sound Output (Min)	(dB)	> or = 90
Resonant Frequency	(Hz)	4000 $\pm$ 500
Operating Temp	(C)	-20~+70
Storage Temp	(C)	-30~+80
Weight	(g)	3
Dimension	mm	24 x H7.5
*Value applying at rated voltage		
*distance for measurement 10cm		

FREQUENCY RESPONSE

