



TEL: 973-328-3200 FAX: 973-328-31

DAFLEX Braided Fiberglass Sleeving UL VW-1

For High Temperature Applications to 1200°F

Description: Daflex D1200 sleeving is an extremely flexible, tightly braided class C fiberglass sleeving. It is non-flammable and treated for removal of all organic matter. The glass braid is fray resistant and non-corroding. It will provide maximum mechanical strength.

Dielectric strength determined by space factor.

It will not support combustion or fungus growth.

This series is RoHS compliant.

DAFLEX Catalog No.	Size	Nom. I.D.		Std. Spool or Coil
		IN.	MM.	
D1200-24	24	0.022	0.56	100', 1000'*
D1200-22	22	0.027	0.69	100', 1000'*
D1200-20	20	0.034	0.86	100', 1000'*
D1200-18	18	0.042	1.07	100', 1000'*
D1200-17	17	0.047	1.19	100', 1000'*
D1200-16	16	0.053	1.35	100', 1000'*
D1200-15	15	0.059	1.50	100', 1000'*
D1200-14	14	0.066	1.68	100', 1000'*
D1200-13	13	0.076	1.93	100', 1000'*
D1200-12	12	0.085	2.16	100', 500'*
D1200-11	11	0.095	2.41	100'*
D1200-10	10	0.106	2.69	100', 500'*
D1200-9	9	0.118	3.00	100'*
D1200-8	8	0.133	3.38	100', 500'*
D1200-7	7	0.148	3.76	100'*
D1200-6	6	0.166	4.22	100', 500'*
D1200-5	5	0.186	4.72	100'*
D1200-4	4	0.208	5.28	100', 500'*
D1200-3	3	0.234	5.94	100'*
D1200-2	2	0.263	6.68	100', 500'*
D1200-1	1	0.294	7.47	100'
D1200-0	0	0.330	8.38	100'
D1200-3/8	3/8"	0.387	9.83	100'
D1200-7/16	7/16"	0.450	11.43	100'
D1200-1/2	1/2"	0.512	13.00	100'
D1200-5/8	5/8"	0.640	16.26	100'
D1200-3/4	3/4"	0.768	19.51	100'
D1200-7/8	7/8"	0.893	22.68	100'
D1200-1"	1"	1.018	25.86	100'

* Preferred Put Up

Standard Color: Natural.

Applicable Specs:NEMA VS-1 1962. Class C, UL STD 1441.